

TNC Female Short Circuit Connector Cap

RF connector dust cap SC2183 from Fairview Microwave is constructed with a TNC connection and has a female gender. This TNC female dust cap is designed as shorting and the body is nickel plated to ensure its durability. The shorting TNC connector cap from Fairview Microwave is in-stock for same day shipment.

RF dust caps are essential for precision connectors to protect them from dust, corrosion and other potential damage especially when using on test and measurement equipment. Some RF connector cap models are designed with a chain to prevent loss or misplacement. Internal shorting connector cap models are available and help to protect equipment from a spike in current commonly caused by ESD (Electro Static Discharge).

Mechanical Specifications

Configuration
 Connector

TNC Female Shorting

Description	Material	Plating
Contact	Brass	Gold
Body	Brass	Nickel

Size

Length 0.67 in [17.02 mm]
 Width 0.57 in [14.48 mm]
 Weight 0.031 lbs [14.06 g]

Environmental Specifications

Temperature

Operating Range -65 to +165 deg C

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

RoHS Compliant Yes
 REACH Compliant 12/17/2015



Features:

- Protects against dust and contaminants
- Protects against physical damage
- Nickel Plated Body
- Internally Shorted

Applications:

- General Purpose Laboratory Use
- Test and Measurement
- ESD Protection

Fairview Microwave
 1130 Junction Dr. #100
 Allen, TX 75013
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Plotted and Other Data

Notes:


TNC Female Short Circuit Connector Cap from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [TNC Female Short Circuit Connector Cap SC2183](#)

URL: <https://www.fairviewmicrowave.com/tnc-female-short-circuit-connector-cap-14-ghz-sc2183-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





STANDARD TOLERANCES	
DECIMAL	
.XX	±0.02
.XXX	±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC.		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		DWG NO		CAGE CODE	
TITLE TNC Female Short Circuit Connector Cap		SC2183		3FKR5	
CAD FILE	041316	SHEET	SCALE	N/A	SIZE A 3045