


HYBRID, D-SUB 7-PIN MALE		SPECIFICATIONS	
PIN #	DESCRIPTION		
A1	VDD	28 VDC	
A2	GND	Ground	
1	ENABLE	Amplifier Enable: TTL Logic High (3.3V) (Internally Pulled-Low)	
2	TEMP SENSE	Analog voltage relative to Module's Temperature @ 10 mV/°C	
3	CURRENT SENSE	Analog voltage relative to IDD @ 100mV per Ampere	
4	NC	No electrical connection	
5	GND	Ground	



- NOTES:
- ADEQUATE HEATSINK REQUIRED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVISION CONTRARY TO U.S. LAW PROHIBITED.



TITLE

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS

THIRD-ANGLE PROJECTION

TOLERANCES:

X = ±.2	[.008]	FRACTIONS	12 [305] < L ≤ 60 [1524] = ±.2 [51] / -0
XX = ±.02	[.51]		60 [1524] < L ≤ 120 [3048] = ±.4 [102] / -0
XXX = ±.005	[.13]	ANGLES ± 1°	120 [3048] < L ≤ 300 [7620] = +.6 [152] / -0

THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.

ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.

SCALE

SIZE	GAGE CODE	DRAWN BY	PART NUMBER	REV
A	3FKR5	K.DANG	FMAM5072	A