



2.2-5 MALE

FM-1/4SFHC (SEE NOTE 1)

(SEE NOTE 2)

4.3-10 FEMALE 4 HOLE FLANGE

www.fairviewmicrowave.com fmca2366 S/N: XXXXXXXXX

PIM LEVEL -zzzdBc S/N: XXXXXXXXX

NOTES:

- CABLES 84" AND UNDER HAVE 1 LABEL CENTERED. CABLES OVER 84" HAVE 2 LABELS, ONE AT EACH END 12.0" FROM THE END OF THE CONNECTOR. 6" FROM CABLE END 1 PLACE FOR ALL LENGTHS OF CABLE.

Ņ

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.





III III III

						'Ө
⊳ ⁱ	SIZE		X=±.2 [5.08] FRACTIONS XX=±.02 [.51] ±1.032 XXX=±.005[.13] ANGLES±1°			ONI
3F	CAGE CODE	ALL DIN			TOLERANCES:	ESS OTHER
3FKR5	7 	IENSIONS S			ANCES:	DIMENSION
MVEER MVEER		HOWN ARE			CAF	SIN[] ARE
MVEERAPPAN	~	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY	048] < L ≤ 30 300 [7	L ≤ 12 [305] = +1 [25] / -0 12 [305] < L ≤ 60 [1524] = +2 [51] / -0 60 [1524] < L ≤ 120 [3048] = +4 [102] / -0	CABLE LENGTH (L) TOLERANCES:	UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS
2	ITEM NO	ENCE ONLY	L ≤ 300 [7620] = +6 [152] / · · · · · · · · · · · · · · · · · ·	L ≤ 12 [305] = +1 [25] / -0 L ≤ 60 [1524] = +2 [51] / -0 ≤ 120 [3048] = +4 [102] / -1	I (L) TOLER	RS ARE II
		.`			NCES:	NCHES
FMCA2366		SCALE	SHEET	DESIG IS 1 FAIRVIEW M ALL	ᠴ	1 HR
		N/A	1 OF	DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION ALL RIGHTS RESERVED.	THE INFORMATION AND	THIRD-ANGLE PROJECTION
Þ.	RF<		1	Y OF DRPORATION. RVED.	AND	ECTION