

| ⋗               | REV.        |           |
|-----------------|-------------|-----------|
| INITIAL RELEASE | DESCRIPTION | REVISIONS |
| 10/03/2021      | DATE        |           |
| SELLIS          | APPROVED    |           |





## NOTES:

- CABLES 84" AND UNDER HAVE 1 LABEL CENTERED. CABLES OVER 84" HAVE 2 LABELS, ONE AT EACH END 12.0" FROM THE END OF THE CONNECTOR. 6" FROM CABLE END 1 PLACE FOR ALL LENGTHS OF CABLE.

Ņ

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFICATION OF THE PROHIBITED OF THE PROHIBITE





III III III

|                    |  |  |  | an INFINIT® brand                          |                              | Fairview Microwave  |
|--------------------|--|--|--|--|------------------------------|---|
| A<br>Size          |  |  | × × ×  | × "  |                              |   |
| CAGE CODE<br>3FKR5 | ALL DIMENSIONS S                             |  | .XX = ±.02 [.51] ± 1/32<br>.XX = ± 0.05[ 13] ANGLES + 1° | + 2 [5 08] FRACTIONS                       | TOLERANCES:                  | LESS OTHERWISE SPEC   |
| MVEERAPPAN         | ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. | 120 [3048]   |  |  | CABLE LENGTH (L) TOLERANCES: | UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS |
| ITEM NO. FMC       | NCE ONLY.                                    | < L ≤ 300 [7620] = +6 [152] / -0<br>300 [7620] < L = +5%L / -0 | [3048] = +2[51]/-0<br>[3048] = +4[102]/-0                | L ≤ 12 [305] = +1 [25] / -0                | L) TOLERANCES:               | ONS ARE INCHES  |
| A2378              | SCALE  | SHEET 1  | FAIRVIEW MICROWAVE CORPORATI<br>ALL RIGHTS RESERVED.     | DESIGN IN THIS DOCUMENT IS THE PROPERTY OF |                              | THIRD-ANGLE   |
| PEV A              | N/A  | OF 1   | VE CORPORATION.<br>RESERVED.                             | S DOCUMENT<br>SERTY OF                     |                              | D-ANGLE PROJECTION  |