




A INI	REV. D	
INITIAL RELEASE	DESCRIPTION	REVISIONS
12/10/2021	DATE	
A. GANWANI	APPROVED	








RECOMMENDED MOUNTING HOLE

4.00[.157] MAX PANEL THICKNESS



MM [INCH]

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



an INFINIT® brand

TITLE

⊳	SIZE			× × × × × × × × × × × × × × × × × × ×		UNL
3F	CAGE CODE	ALL DIM	000[0]	$X = \pm .2$ [5.08] $XX = \pm .02$ [.51]	TOLERANCES:	ESS OTHER
3FKR5		ENSIONS SHO	() ()	X = ±.2 [5.08] FRACTIONS XX = ±.02 [.51] ± 1/32 XXX = +.005 [.13] ANGLES + 1°	NCES:	WISE SPECIFI DIMENSIONS
K.DANG	DRAWN BY	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.	120 [3048] < L ≤ 300 300 [762	L ≤ 12 12 [305] < L ≤ 60 60 [1524] < L ≤ 120	CABLE LENGTH (L) TOLERANCES	UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS
FMCN0009	NCE ONLY.	120 [3048] < L ≤ 300 [7620] = +6 [152] / -0 300 [7620] < L = +5%L / -0	L ≤ 12 [305] = +1 [25] / -0 12 [305] < L ≤ 60 [1524] = +2 [51] / -0 60 [1524] < L ≤ 120 [3048] = +4 [102] / -0	L) TOLERANCES:	ONS ARE INCHES	
10009		SCALE N	SHEET 1 C	DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION ALL RIGHT'S RESERVED.	THE INFORMATION AND	THIRD-ANGLE PROJECTION
⊳	REV	N/A)F 2	OCUMENT RTY OF CORPORATION. SERVED.	ON AND	OFECTION