

STRIPPING DIMENSIONS

ASSEMBLY PROCEDURES

- 1. STRIP CABLE AS SHOWN. DO NOT NICK CENTER CONDUCTOR.
- 2. SLIDE CABLE INTO CONNECTOR INSURING CENTER CONDUCTOR MATES WITH CENTER PIN.
- 3. OUTER CONDUCTOR BOTTOMS OUT WITH BODY SHOULDER, SOLDER OUTER CONDUCTOR TO BODY.

| TOLERANCES | .X ±0.2 .XX ±0.1 .XXX ±0.05 | Æ |
|------------|-----------------------------------|---|
|------------|-----------------------------------|---|

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRV

ALLEN, TX 750

TITLE

| | | VIEW MICROWAVE INC. |
|-----------------------|-------------|--|
| CAD FILE 022117 SHEET | DWG NO | NOTES: 1. UNLESS 2. ALL SPE 3. DIMENSI |
| 022117 | F | OTHERWIS DIFICATION ONS ARE I |
| SHEET | FMCN1195 | NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm]. |
| SCALE N/A SIZE A 2233 | CAGE | ONS ARE NOV SE WITHOUT N |
| SIZE A | CAGE CODE 3 | INAL. IOTICE AT AI |
| 2233 | 3FKR5 | NY TIME. |
| | | |