


CRIMP SIZE REQUIRED CONTACT: SOLDER FERRULE: 213" HEX CRIMP TOOL



THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS.



an INFINIT® brand

Þ	SIZE	
3FKR5	CAGE CODE	ALL DIMENSIONS SH
DMAY	DRAWN BY	OWN ARE FOR REFERE
FMCN1354	ITEM NO.	REFERENCE ONLY.
J1354		Z
Þ	REV	/A

 $X = \pm .2$ [5.08] $XX = \pm .02$ [.51] $XXX = \pm .005$ [.13]

FRACTIONS ± 1/32 ANGLES ± 1°

L ≤ 12 [305] = +1 [25] / -0
12 [305] < L ≤ 60 [1624] = +2 [51] / -0
60 [1524] < L ≤ 120 [3048] = +4 [102] / -0
120 [3048] < L ≤ 300 [7620] = +6 [182] / -0
300 [7620] < L = +5%L / -0

THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICKOWAVE CORPORATION.
ALL RIGHTS RESERVED.

CABLE LENGTH (L) TOLERANCES: