

A INITIAL RELEASE	REV. DESCRIPTION	
LEASE	PTION	REVISIONS
02/11/2022	DATE	
A.GANWANI	APPROVED	





STRIPPING DIMENSIONS

CRIMP SIZE REQUIRED

CONTACT: SOLDER.
RERRULE: .213" [5.41] HEX CRIMP TOOL.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



an INFINITe brand

TITLE

Þ	SIZE	ALL DIN	X = ±.2 [5.08] FRACTIONS XX = ±.02 [.51] ±1/32 XXX = ±.005[.13] ANGLES ± 1°				CN
ب	CAGE CODE					TOLERANCES	ОПП ПП
ת ע		IENSIONS SHO			EBACTIONS	ANCES:	DIMENSIONS
K GI FROVA	DRAWN BY	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.			CABLE LENGTH (L) TOLERANCES:	ONLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES	
FMCN1815	ITEM NO.	NCE ONLY.	L \(\frac{3}{3}\)0 \([7620] = \(+6\) \([152] \/ \cdot \) 300 \([7620] \< L = \(+5\) \(L \/ \cdot \)	12 [305] < L ≤ 60 [1524] = +2 [51] / -0 60 [1524] < L ≤ 120 [3048] = +4 [102] / -0	L ≤ 12 [305] = +1 [25] / -0	L) TOLERANCES:	ON ART NOTED
11815		SCALE N	SHEET 1	FAIRVIE	DESIGN IN THIS DOCUMENT	THE INFORMATION AND	+
Þ	REV	N/A	OF 1	CORPORATION. SERVED.	RTYOF	ON AND	