


.44 [11.1] REF.

.311 [7.90]

.500 [12.70]

1.34



## STRIPPING DIMENSIONS

## CRIMP TOOL REQUIRED

CONTACT: .043" [1.09] HEX CRIMP TOOL. FERRULE: .255" [6.48] HEX CRIMP TOOL.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES



an INFINIT® brand

TITLE

A CA		UNLESS OTH  TOLEI  X = ±.2 [5.08]  XX = ±.02 [.51]  XXX = ±.005[.13]	
3FXR5	LL DIMENSIONS S	UNLESS OTHERWISE SPECIF DIMENSIONS TOLERANCES:  X = ±.2 [5.08] FRACTIONS XX = ±.02 [.51] ± 1/32 XXX = ±.005[.13] ANGLES ± 1°	
K.GLEBOVA FMCN1824	OR REFEREN	IN [] ARE MILLIMETERS  CABLE LENGTH (L) TOLERANCES:  L \$ 12 [305] = +1 [25] / -0  12 [305] < L \$ 60 [1524] = +2 [51] / -0  60 [1524] < L \$ 120 [3048] = +4 [102] / -0  120 [3048] < L \$ 300 [7620] = +6 [152] / -0  300 [7620] < L = +5%L / -0	
11824 REV	SCALE N/A	THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE REPORT OF FAIRWER WINGROWN/WE CORPORATION ALL RIGHTS RESERVED.  SHEET  1  OF  1	
		-	1