

NOTES:

STRIPPING DIMENSIONS

- . `
- CABLE ATTACHMENT:
 OUTER: CRIMP.
 INNER:SOLDER.
- 2 CRIMP SIZE REQUIRED: FERRULE: .151" [3.84] HEX. CRIMP TOOL

ASSEMBLY PROCEDURES

- STRIP CABLE AS SHOWN. SLIDE FERRULE OVER CABLE.
- 2 INSTALL CABLE INTO BODY OF CONNECTOR AND SOFT SOLDER CENTER CONDUCTOR IN PLACE.
- ω CRIMP FERRULE, INSERT INSULATOR AND SCREW CAP.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES



an INFINIT® brand

III III III



						'	
⊳	SIZE		X X X X X X X X X X X X X X X X X X X			TOLER	Q E
ω	CAGE CODE	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.	X=±.2 [5.08] XX=±.02 [.51] XXX=±.005[.13]		1 00 01 11		
3FKR5			X = ±.2 [5.08] FRACTIONS XX = ±.02 [.51] ± 1.02 XXX = ±.005 [.13] ANGLES ± 1° 12 [30.6] < L ≤ 60 [152.4] = ± 2 [51] / -0 2XXX = ±.005 [.13] ANGLES ± 1° 120 [30.6] < L ≤ 200 [762.0] = +6 [152] / -0 300 [762.0] < L = ±5%L/ -0			TOLERANCES:	DIMENSIONS IN [] ARE MILLIMETERS
K.GLEBOVA	DRAWN BY					CABLE LENGTH (L) TOLERANCES:	IN [] ARE N
EBOVA	,						AILLIMETER
	ITEM NO.	ENCE ONLY				(L) TOLER	S CNO AKE
FMCN1822		·	ANCES: 1 [25] / -0 2 [51] / -0 4 [102] / -0 6 [152] / -0 5%L / -0				
		SCALE N/A	THE DESK IS FAIRVIEW NALL SHEET				
			1 c	THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FIEW MICROWAVE CORPORA ALL RIGHTS RESERVED.			
≻	REV	/A	1 1	FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.	OCUMENT ATY OF	ON AND	ф Ф