


STRIPPING DIMENSIONS

NOTES:

- CABLE ATTACHMENT:
- OUTER: CRIMP. INNER: SOLDER.

- 2. CRIMP SIZE REQUIRED:CONTACT: SOLDER.FERRULE: .151" [3.84] HEX. CRIMP TOOL.



THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT
ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO U.S., LAW PROHIBITED.

INJECT OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES



an INFINIT® brand

TITLE

⊳	SIZE		X=±.2 [5.08] FRACTIONS XX=±.02 [.51] ±1/32 XXX=±.005[.13] ANGLES±1°			TOLERANCES:	QN E
3FKR5	CAGE CODE	ALL DIMENSIONS SH					DIMENSIONS
K.GLEBOVA	DRAWN BY	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.			L ≤ 1;	CABLE LENGTH (L) TOLERANCES:	UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES
FMCN1841	ITEM NO.	NCE ONLY.	10 [7620] = +6 [152] / -0 300 [7620] < L = +5%L / -0	L ≤ 12 [305] = +1 [25] / -0 12 [305] < L ≤ 60 [1524] = +2 [51] / -0 60 [1524] < L ≤ 120 [3048] = +4 [102] / -0		(L) TOLERANCES:	ONG ARE INCHES
11841	REV	SCALE N/A	THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE REPORT OF FARRYER MAL RIGHTS RESERVED. SHEET 1 1 THE INFORMATION AND DESIGN IN THE INFORMATION AND DESIGN IN THE INFORMATION AND IN THE INFORMATION ALTRIGHTS RESERVED.				TIND-ANGLE PROJECTION
>	<		_	OF PORATION. VED.	MENT		