

ı			
	≻	REV.	
	INITIAL RELEASE	DESCRIPTION	REVISIONS
	02/11/2022	DATE	
	A.GANWA	APPROVED	






STRIPPING DIMENSIONS

## NOTES:

- OUTER: CRIMP.
   INNER: SOLDER.
- 2. CRIMP SIZE REQUIRED:
- CONTACT: SOLDER.
  FERRULE: .151" [3.84] HEX. CRIMP TOOL.



THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



an INFINIT® brand

TITLE

A A		3000	× × × = = + + + + +		UNL
CAGE CODE	ALL DIV		X = ±.2 [5.08] X = ±.2 [5.1] XX = ±.005[.13]		ESS OTHEI
DIMENSIONS SHO		X = ±.2 [5.08] FRACTIONS XX = ±.02 [.51] ±1/32 XXX = ±.005[.13] ANGLES ± 1°		TOLERANCES:	DIMENSIONS
DRAWN BY K.GLEBOVA	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.	_		CABLE LENGTH (L) TOLERANCES	UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS
ITEM NO. FMCN 1842	NCE ONLY.	120 [3048] < L ≤ 300 [7620] = +6 [152] / -0 300 [7620] < L = +5%L / -0	L ≤ 12 [305] = +1 [25] / -0 12 [305] < L ≤ 60 [1524] = +2 [51] / -0 60 [1524] < L ≤ 120 [3048] = +4 [102] / -0	L) TOLERANCES:	ONS ARE INCHES
11842	SCALE N	SHEET 1	DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION ALL RIGHTS RESERVED.	THE INFORMATION AND	THIRD-ANGLE PROJECTION
REV A	N/A	¥ 1	OCUMENT RTY OF CORPORATION. SERVED.	ON AND	-\-\-\-\-\-\-\-\-\-\-\-\-\-\-\-\-\-\-\