

A REV.	
DESCRIPTION INITIAL RELEASE	REVISIONS
DATE 02/11/2022	
A.GANWANI	





STRIPPING DIMENSIONS

<u>CRIMP SIZE REQUIRED:</u>CONTACT: SOLDER.FERRULE: .100" [2.54] HEX. CRIMP TOOL.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT
ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO U.S., LAW PROHIBITED.

INJECT OF THE PROME SPECIFIED LEADING DIMENSIONS ARE INCHES.

Fairview Microwave

an INFINIT® brand

TITLE

A SIZE			XXX : : : : : : : : : : : : : : : : : :	× = + 2		Q L
CAGE CODE	ALL DIM	[5.08] [.51] 5[.13]			TOLERANCES:	- SS CIHER
3FKR5	ENSIONSS	FRACTIONS ± 1/32 ANGLES ± 1'			NCES:	DIMENSION
DRAWN BY	HOWN AF	_	•	_	ြင	IN [] AF
K.GLEBOVA	E FOR REFE	[3048] < L ≤ 3 300	L: 12 [305] < L ≤ 1 1524] < L ≤ 1 3048] < L ≤ 3			DIMENSIONS IN [] ARE MILLIMETERS
ITEM NO.	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.	120 [3048] < L ≤ 300 [7620] = +6 [152] / -0 300 [7620] < L = +5%L / -0	$ z 305 < L \le 60 1524 = +2 51 / -0$ $ 50 1524 < L \le 120 3048 = +4 102 / -0$	L ≤ 12 [305] = +1 [25] / -0	CABLE LENGTH (L) TOLERANCES:	DIMENSIONS IN [] ARE MILLIMETERS
FMCN1848	SCALE N	THE INFORMA DESIGN IN THIS IS THE PROPI FAIRVIEW MICROWAV ALL RIGHTS R SHEET 1				
PEV P	N/A	OF 1	SERVED.	DOCUMENT RTY OF	ION AND	THIRD-AWGLE PROGEDITION