





STRIPPING DIMENSIONS

CRIMP SIZE REQUIRED

FERRULE: .213" [5.41] HEX. CRIMP SIZE.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO U.S., LAW PROHIBITED.

ONLY



TITLE

	-						
>	SIZE C	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.	X=±.2 [5.08] FRACTIONS XX=±.02 [.51] ± 1/32 XXX=±.005[.13] ANGLES±1° 120 [3048] < L ≤ 300 300 [76:2]				
SEKRA	CAGE CODE					TOLERANCES:	□
						CES:	MENSIONS
K GI FROVA	DRAWN BY					CABLE LENGTH (L) TOLERANCES	DIMENSIONS IN [] ARE MILLIMETERS
EMCN1846	ITEM NO.	NCE ONLY.	12 [305] < L ≤ 12 [305] = +1 [25] / 0 12 [305] < L ≤ 60 [1524] = +2 [51] / 0 60 [1524] < L ≤ 120 [3048] = +4 [102] / 0 120 [3048] < L ≤ 300 [7620] = +6 [152] / 0 300 [7620] < L = +5%L / 0			L) TOLERANCES:	0
	SC A		SHEET 1	DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPOC ALL RIGHTS RESERVED SHEET OF OF			∌
>	REV	N/A	OF 1	FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.	DESIGN IN THIS DOCUMENT	THE INFORMATION AND	‡