



 $\phi.280^{+.005}_{-.000} \\
\left[7.11^{+0.13}_{-0.00}\right]^{-}$

 $.270^{+.005}_{-.000}$ $\left[6.86^{+0.13}_{-0.00}\right]$

MOUNTING HOLE

STRIPPING DIMENSIONS

[2.54].100

ASSEMBLY PROCEDURE

- STRIP CABLE AS SHOWN. DO NOT NICK CENTER CONDUCTOR.
- 2 CHAMFER CENTER CONDUCTOR AS SHOWN.
- ω INSERT CABLE INTO CONNECTOR BODY, MATING THE CENTER CONDUCTOR WITH THE CONTACT.
- 4. SOLDER CABLE TO CONNECTOR BODY.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.





HITE



P | SIZE $X = \pm .2$ [5.08] $XX = \pm .02$ [.51] $XXX = \pm .005$ [.13] UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS CAGE CODE 3FKR5 ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. FRACTIONS ± 1/32 ANGLES ± 1° AKRESOWSK $\begin{array}{c} L \leq 12 \left[305\right] = +1 \left[25\right] / o \\ 12 \left[305\right] < L \leq 60 \left[1524\right] = +2 \left[57\right] / o \\ 60 \left[1524\right] < L \leq 120 \left[3046\right] = +4 \left[102\right] / o \\ 120 \left[3046\right] < L \leq 300 \left[7620\right] = +6 \left[152\right] / o \\ 300 \left[7620\right] < L = +5\% L / o \\ \end{array}$ CABLE LENGTH (L) TOLERANCES: ITEM NO. FMCN1891 THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION.
ALL RIGHTS RESERVED. N/A REV