




REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
B	FOR-REVISED DIMENSIONS	03/24/2022	AGANWANI



STRIPPING DIMENSIONS

ASSEMBLY PROCEDURE

1. STRIP CABLE AS SHOWN. DO NOT NICK CENTER CONDUCTOR.
2. SLIDE CABLE INTO CONNECTOR, ENSURING CENTER CONDUCTOR MATES WITH CENTER PIN.
3. OUTER CONDUCTOR BOTTOMS OUT WITH BODY SHOULDER. SOLDER OUTER CONDUCTOR TO CONNECTOR BODY.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



TITLE

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS		THIRD-ANGLE PROJECTION	
TOLERANCES:		THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.	
CABLE LENGTH (L) TOLERANCES:		SCALE	
L ≤ 12 [305] = +1 [25] / -0		1	
12 [305] < L ≤ 60 [1524] = +2 [51] / -0		OF	
60 [1524] < L ≤ 120 [3048] = +4 [102] / -0		1	
120 [3048] < L ≤ 300 [7620] = +6 [152] / -0		1	
300 [7620] < L = +5% / -0		N/A	
SIZE	GAGE CODE	DRAWN BY	ITEM NO.
A	3FKRS	AKRESOWSK	FMCN1887
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.			REV
			B