

A	REV.	
INITIAL RELEASE	DESCRIPTION	REVISIONS
8/17/2022	DATE	
AGANWANI	APPROVED	







THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES

Fairview Microwave

an INFINIT® brand

⊳	SIZE			× × × × ×		9	
3FKR5	CAGE CODE	ALL DIMENSIONS SHO	X = ±.2 [5.08] FRACTIONS  XX = ±.02 [.51] ±1/32  XXX = ±.005[.13] ANGLES ± 1°  ANGLES ± 1°  12 [30.5] < L ≤ 60 [152.4] = +2 [51] / -0  60 [152.4] < L ≤ 102 [30.6] = +4 [102] / -0  200 [30.4] < L ≤ 102 [30.6] = +4 [102] / -0  300 [7620] < L = +5%L / -0  ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.		OLERANCES:	ONLINE OF THE PROPERTY OF THE	
PSRINIVAS	DRAWN BY	OWN ARE FOR REFEREI			CABLE LENGIH (L) I OLERANCES	DIMENSIONS IN [] ARE MILLIMETERS	
ITEM NO. FMCN1933		NCE ONLY.	L ≤ 12 [305] = +1 [25] / 0 12 [305] < L ≤ 60 [1824] = +2 [51] / 0 60 [1524] < L ≤ 120 [3048] = +4 [102] / 0 120 [3048] < L ≤ 300 [7620] = +6 [152] / 0 300 [7620] < L = +5%L / -0		L) TOLERANCES:		
11933		SCALE N/A	DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION ALL RIGHTS RESERVED. SHEET OF 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1			THE INECORMATION AND	
⊳	REV	A	1	OCUMENT TY OF CORPORATION. ERVED.	DN AND	4	