



NOTES:
1. HERMETICITY OF 1x10⁻⁶cc/sec.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



an INFINITE brand
TITLE

>	SIZE CAC	ALL DIMENSION:	X = ±.2 [5.08] .XX = ±.02 [.51] .XXX = ±.005[.13]			IĦ		
SEKRS	CAGE CODE		X=±.2 [5.08] FRACTIONS XX=±.02 [.51] ±1/32 XXX=±.005[.13] ANGLES±1°			TOLERANCES:	DIMENS	
DRA		S SHOWN A	_				ONS IN []	
DMAY	DRAWN BY	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.	L ≤ 12 [305] = +1 [25] / 0 12 [305] < L ≤ 60 [1824] = +2 [51] / -0 60 [1824] < L ≤ 120 [3048] = +4 [102] / -0 120 [3048] < L ≤ 300 [7620] = +6 [152] / -0 300 [7620] < L = +5%L / -0		L ≤ 1:	CABLE LENGTH (L) TOLERANCES:	UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS	
EMCN45838	ITEM NO.	NCE ONLY.	L \(\le 300 \left[7620 \right] = +6 \left[152 \right] \right -0 \\ 300 \left[7620 \right] \left \Left = +5% \Light[7.0 \right] \)	12 [305] < L < 60 [1524] = +2 [51] /-0 60 [1524] < L < 120 [3048] = +4 [102] /-0	L ≤ 12 [305] = +1 [25] / -0	L) TOLERANCES:		
		SCALE N	SHEET 1 C	FAIRVIEW MICROWAVE CORPORATION ALL RIGHTS RESERVED.	DESIGN IN THIS DOCUMENT	(+	I I X V-ANGLE TX COEC I CN
Þ	REV	N/A	<u> </u>	CORPORATION. SERVED.	OCUMENT		+	OJECTION