







LABEL:

FAIRVIEW MICROWAVE FMCP1153 D/C: YYWW

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



an INF

TITLE

SIZE.

A 3FI	E CAGE CODE	ALL DIME	TOLERANGES: X = ±.2 [5.08] FRAC (X = ±.02 [.51] ±: (X = ±.005[.13] ANGL	-
3FKR5		WOHS SNOISN	FRACTIONS ± 1/32 ANGLES ± 1°	UNLESS OTHERWOSE SPECIFIED LEAUNING UMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS TO FRANCES: CARLET FROM 1 TO FRANCES
K.DANG	DRAWN BY	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.	CABLE LENG IH (L) TO LERANCES: L ≤ 12 [305] = +1 [25] /-0 12 [305] < L ≤ 60 [1524] = +2 [51] /-0 60 [1524] < L ≤ 120 [3048] = +4 [102] /-0 120 [3048] < L ≤ 300 [7620] = +6 [152] /-0 300 [7620] < L = +5%L /-0	DIMENSIONS IN [] ARE MILLIMETERS
FMCP1153	ITEM NO.	NCE ONLY.	ABLE LENGTH (L) TOLEPANCES: L ≤ 12 [305] = 41 [25] / 0 12 [305] < L ≤ 60 [1824] = +2 [51] / 0 [1824] < L ≤ 120 [3048] = +4 [102] / 0 [3048] < L ≤ 300 [7620] = +6 [152] / 0 300 [7820] < L = +5%L / 0	
		SCALE N	THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRNIEW MICROWAVE CORPOPATION ALL RIGHTS RESERVED. SHEET OF 1 THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRNIEW MICROWAVE CORPOPATION SHEET OF 1 THE INFORMATION AND DESIGN IN THE INF	•
Þ	REV	N/A	TITION AND DOCUMENT ERTY OF YE CORPORATION. RESERVED. OF 1	4