

6

5


4

3

2

1

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	03/23/2023	HBAKKE	AGANWANI




FEATURES:

1. STRIPS COAXIAL CABLE RG59, RG6 OF THE STUB END IN MDU BOX, WALL OUTLET OR OTHER TIGHT SPACES.
2. SPINS AROUND AS A SCREWDRIVER MOTION FOR STRIPPING.
3. USES BLACK VELCRO FOR FOLDING BACK THE BRAIDED SHIELD OF CABLE.
4. DESIGNED WITH INTERCHANGEABLE CASSETTE & STRIPPING LENGTH 6mm (1/4").

CABLE TYPE	STRIPPING LENGTH (D):
RG59/6 COAXIAL CABLE (OUTER JACKET THICKNESS 0.85mm)	<p>2 BLADES MODE</p> <p>D= 6mm (1/4") D1=8mm(5/16")</p>

WORKS IN TIGHT SPOTS.



UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

.X = ±.2 [5]	FRACTIONS
.XX = ±.02 [.5]	± 1/32
.XXX = ±.005 [.13]	ANGLES ± 1°

CABLE LENGTH TOLERANCES:

≤12 [305]	= +1 [25] / -0
>12 [305] ≤ 60 [1524]	= +2 [51] / -0
>60 [1524] ≤ 120 [3048]	= +4 [102] / -0
>120 [3048] ≤ 300 [7620]	= +6 [152] / -0
>300 [7620]	= +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE.

Fairview Microwave
an INFINIT® brand

Website: www.FairviewMicrowave.com
Phone: 1.800.715.4396 | 1.972.649.6678

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5

SCALE	SHEET
NONE	1 OF 1

DESCRIPTION
Tool, RG59/6 (Thickness 0.85mm) Front-Loaded Rolling Motion

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	3FKR5	HBAKKE	FMTL5211	A

6

5

4

3

2

1