



TGALLA	8/16/2022	INITIAL RELEASE	А
APPROVED	DATE	DESCRIPTION	REV.
		REVISIONS	










NOTES:

- N MATERIAL: 1/2 HARD BRASS LABEL PER ILS-100-03. FOR INTERNAL REFERENCE ONLY. LABEL LOCATION FOR REFERENCE ONLY.
- ယ SERIAL NUMBER AND DATE CODE EX: SN: 5XZY2U, DC: 2232



THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

Fairview Microwave

an INFINIT® brand



A SIZE		X X X = = ±	UNLE
CAGE CODE	ALL DIM	$X = \pm .2$ [5.08] $XX = \pm .02$ [.51] $XXX = \pm .005$ [.13]	TOLERANCES:
3FKR5	ENSIONS SH	FRACTIONS ± 1/32 ANGLES ± 1°	DIMENSION ANCES:
DRAWN BY	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY		UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS TOLERANCES: CABLE LENGTH (L) TOLERANCES
ITEM NO. FMM	NCE ONLY.	12 [305] < L 5 00 [1824] = 22 [51] / -0 60 [1524] < L 5 120 [3048] = +4 [102] / -0 120 [3048] < L 5 300 [7820] = +6 [182] / -0 300 [7820] < L 5 500 [7820] <	ARE MILLIMETERS CABLE LENGTH (L) TOLERANCES:
FMMT3011 REV	SCALE N/A	FAIRV	THE INFORMATION AND DESIGN IN THIS DOCUMENT