

WR-284 Twistable Flexible Waveguide in 12 Inch Using UG Round Cover Flange with a 2.6 to 3.95 GHz Frequency Range



FM-W284TF001-12

Features

- · WR-284 waveguide
- · Flexes in both the E and H plane
- · 2.6 GHz to 3.95 GHz Frequency Range

Applications

- · Allows expansion/contraction due to thermal issues
- · Test Benches
- · Microwave Radio

- Brass flanges with a brass body
- Neoprene sleeve provides added protection and mechanical support
- · Eliminates installation problems caused by misalignment
- · Provides vibration isolation

Description

The FM-W284TF001-12 is part of Fairview Microwave's family of flexible, twistable waveguides which operates in the 2.6 to 3.95 GHz range. The waveguide body is made of a helically wound silver coated brass strip. It can be twisted and/or bent in both the E and H planes without impairing VSWR or attenuation. The waveguide is covered by a neoprene jacket which protects the waveguide and provides mechanical support

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	2.6		3.95	GHz
VSWR		1.07:1		
Insertion Loss		0.06		dB
Input Power			6.5	kWatts

Electrical Specification Notes: VSWR is per 2 foot. Insertion Loss is dB per foot.

Mechanical Specifications

Waveguide Size
Waveguide Design
Section Length
E-Plane Minimum Bend Radius, One Time
H-Plane Minimum Bend Radius, One Time

WR-284 Twistable 12 in [304.8 mm] 7 in [177.8 mm] 14 in [355.6 mm]

Description	Flange 1	Waveguide	Flange 2
Туре	Round Cover	WR-284	Round Cover
Designation	UG		UG
Material	Brass	Brass	Brass

Temperature

Operating Range

-50 to 100 deg C



WR-284 Twistable Flexible Waveguide in 12 Inch Using UG Round Cover Flange with a 2.6 to 3.95 GHz Frequency Range



FM-W284TF001-12

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Notes, Plotted Data

Typical Performance Data

WR-284 Twistable Flexible Waveguide in 12 Inch Using UG Round Cover Flange with a 2.6 to 3.95 GHz Frequency Range from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: WR-284 Twistable Flexible Waveguide in 12 Inch Using UG Round Cover Flange with a 2.6 to 3.95 GHz Frequency Range FM-W284TF001-12

URL: https://www.fairviewmicrowave.com/wr-284-twistable-flexible-waveguide-ug-round-2.6-3.95-ghz-fm-w284tf001-12-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FM-W284TF001-12 CAD Drawing

WR-284 Twistable Flexible Waveguide in 12 Inch Using UG Round Cover Flange with a 2.6 to 3.95 GHz Frequency Range

