

## Vector Network Analyzer (VNA) Ruggedized 18 GHz Test Cable N Male to N Female in 24 Inch

The type N male to type N female 24 inch cable using Vector Network Analyzer (VNA) ruggedized coax, part number FM18VNA004-24, from Fairview Microwave is in-stock and ships same day. This Fairview type N to type N cable assembly has a male to female gender configuration with 50 ohm flexible VNA-R coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FM18VNA004-24 type N male to type N female cable assembly operates to 18 GHz. The triple shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 90 dB. Fairview's high performance precision VNA test cables are designed to provide highly accurate repeatable test results. These rugged VNA test cables have excellent insertion loss, low VSWR and +/- 2° of phase stability with flexure. The precision stainless steel connectors and spiral stainless steel armoring are designed to limit torsional twist when the cables are flexed. These VNA test cables have a 5,000 mating cycle life when mated with proper care. The cable armoring prevents stress due to over bending and enhances amplitude and phase stability, while maintaining the flexibility required in a test environment. When properly calibrated, these test cables effectively extend the VNA test port to the terminating connector of the cable assembly allowing for accurate measurement of devices that cannot be directly connected to a network analyzer test port.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

| Description                  | Min | Typ          | Max    | Units        |
|------------------------------|-----|--------------|--------|--------------|
| Frequency Range              | DC  |              | 18     | GHz          |
| VSWR                         |     |              | 1.25:1 |              |
| Velocity of Propagation      |     | 70           |        | %            |
| RF Shielding                 | 90  |              |        | dB           |
| Capacitance                  |     | 29.4 [96.46] |        | pF/ft [pF/m] |
| Phase Stability with Flexure |     | ±2           |        | Degrees      |

### Performance by Frequency

| Description           | F1     | F2     | F3     | F4 | F5 | Units |
|-----------------------|--------|--------|--------|----|----|-------|
| Frequency             | 6      | 12     | 18     |    |    | GHz   |
| Insertion Loss (Max.) | 0.86   | 1.3    | 1.66   |    |    | dB    |
| VSWR (Max.)           | 1.25:1 | 1.25:1 | 1.25:1 |    |    |       |
| Power Handling (Max.) |        |        | 88     |    |    | W     |

### Mechanical Specifications

#### Cable Assembly

|         |                       |
|---------|-----------------------|
| Length* | 24 in [609.6 mm]      |
| Weight  | 0.5085 lbs [230.65 g] |



### Configuration:

- N Male
- N Female
- VNA-R

### Features:

- Max Frequency 18 GHz
- Shielding Effectivity > 90 dB
- 70% Phase Velocity
- Triple Shielded
- PET Jacket
- VNA Test Cables Extend VNA Test Ports
- Low VSWR and Low Insertion Loss
- Crush resistant stainless steel cable armor
- Flexible PET protective sleeve
- Connector resist twisting during flexure
- Rugged connector attachment
- Highly stable +/- 2° of phase change under flexure
- Serialized test data provided
- Same day shipment standard length assemblies

### Applications:

- General Purpose
- Test & Measurement
- Laboratory Use
- VNA Test applications
- Production floor testing
- Precision lab testing

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

**Cable**

|                                      |                            |
|--------------------------------------|----------------------------|
| Cable Type                           | VNA-R                      |
| Impedance                            | 50 Ohms                    |
| Inner Conductor Type                 | Solid                      |
| Inner Conductor Material and Plating | Copper, Silver             |
| Dielectric Type                      | PTFE                       |
| Number of Shields                    | 3                          |
| Shield Layer 1                       | Silver Plated Copper Braid |
| Shield Layer 2                       | Silver Plated Copper Tape  |
| Shield Layer 3                       | Silver Plated Copper Braid |
| Jacket Material                      | PET                        |
| Jacket Diameter                      | 0.43 in [10.92 mm]         |

One Time Minimum Bend Radius 4 in [101.6 mm]

**Connectors**

| Description                     | Connector 1                | Connector 2                |
|---------------------------------|----------------------------|----------------------------|
| Type                            | N Male                     | N Female                   |
| Impedance                       | 50 Ohms                    | 50 Ohms                    |
| Contact Material & Plating      | Beryllium Copper, Gold     | Beryllium Copper, Gold     |
| Dielectric Type                 | PTFE                       | PTFE                       |
| Body Material & Plating         | Passivated Stainless Steel | Passivated Stainless Steel |
| Coupling Nut Material & Plating | Passivated Stainless Steel |                            |

Mechanical Specification Notes:  
 Crush Resistance: 1,050 lbs.  
 Jacket Material is a PET weave over a spiral stainless steel sheath

**Environmental Specifications**
**Temperature**

Operating Range +125 deg C

**Compliance Certifications** (see [product page](#) for current document)


**Plotted and Other Data**

Notes:

**How to Order**

Part Number Configuration:

**FM18VNA004 - xx uu**



Example: FM18VNA004-12 = 12 inches long cable  
 FM18VNA004-100cm = 100 cm long cable


Vector Network Analyzer (VNA) Ruggedized 18 GHz Test Cable N Male to N Female in 24 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [Vector Network Analyzer \(VNA\) Ruggedized 18 GHz Test Cable N Male to N Female in 24 Inch FM18VNA004-24](#)

URL: <https://www.fairviewmicrowave.com/n-male-n-female-cable-vna-cable-coax-fm18vna004-24-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





|  |        |   |       |                    |             |
|--|--------|---|-------|--------------------|-------------|
| <b>FAIRVIEW MICROWAVE INC.</b><br>ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM                          |        | NOTES:<br>1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.<br>2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.<br>3. DIMENSIONS ARE IN INCHES [mm]. |       |                    |             |
| TITLE<br>Vector Network Analyzer (VNA) Ruggedized 18 GHz<br>Test Cable N Male to N Female in 24 Inch |        | DWG NO<br>FM18VNA004  |       | CAGE CODE<br>3FKR5 |             |
| CAD FILE   | 072215 | SHEET   | SCALE | N/A                | SIZE A 2233 |