

## 698-960 MHz / 1710-2700 MHz / 3400-4200 MHz Low PIM Rated Indoor/Outdoor V-pol Omni Antenna, 3-4 dBi, Type N Female Connector

The indoor/outdoor omnidirectional FM510M1031 antenna from Fairview Microwave is a high performance, low PIM rated RF component which operates from 698 to 4200 MHz. The FM510M1031 antenna is ideal for 5G, LTE, CDMA, LPWAN/IoT/M2M applications including LoRA, LTE-M, NB-IOT and Distributed Antenna System (DAS) Networks. The Multi-Band design of the Fairview Microwave FM510M1031 antenna can be used for a wide array of in-building wireless applications where wide coverage is desired. Fairview Microwave's FM510M1031 can be used to distribute Cellular and WiFi signals throughout a building or area.

The Type N connectorized FM510M1031 antenna with vertical polarization from Fairview Microwave provides Passive Intermodulation (PIM) ratings better than -150 dBc. The key to providing the best performance in telecommunications is to ensure the components used are low PIM rated. The 698-4200 MHz FM510M1031 with 4 dBi max gain helps meet the increasing demand for higher data rates and the ability to provide streaming video for mobile devices.

The Type N connectorized FM510M1031 antenna from Fairview Microwave excels in large open areas such as indoor courtyards, indoor sporting venues, convention centers and shopping malls. The mounting bracket and hardware are included for easy installation. Fairview Microwave indoor/outdoor omnidirectional with Type N female purchases will ship the same day. Our FM510M1031 antenna is part of over one million RF, microwave and millimeter wave components in stock and ready for same-day shipment worldwide.

### Configuration

Design	Omni
Frequency Range	698 to 4200 MHz
Gain	3 to 4 dBi
Polarization	Vertical
Connector Type	N Female
Number of Ports	1

### Electrical Specifications

Description	Min	Typ	Max	Units
Impedance		50		Ohms
Gain		3		dBi
Gain			4	dBi
Input Power			50	Watts
VSWR			1.8:1	
Passive Intermodulation 3rd Order, 2 x 20 W		-150		dBc

### Specifications by Frequency

Description	Band 1	Band 2	Band 3	Band 4	Band 5	Units
Range	0.698-0.806	0.806-0.96	1.71-2.7	3.4-4.2		GHz
Gain	3.5	3	3.5	4		dBi
Horiz. Beam Width	360	360	360	360		Degrees



### Features:

- Low Passive Intermodulation (PIM) <-150 dBc @ 2x20W
- Vertical Polarization
- Compact and lightweight for indoor or outdoor use
- Type N Female connector
- Covers 5G, WiFi and LTE frequency bands including extended CBRS

### Applications:

- Indoor distribution of 5G, LTE, GSM/CDMA
- In-building public or private networks
- LPWAN, LoRA, LTE-M, NB-IoT, IoT, M2M applications
- MIMO DAS (Distributed Antenna Systems)
- Indoor or Outdoor Applications

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)



