

FMAD1159 DATA SHEET

2.4mm Female to 2.4mm Female Bulkhead Adapter 0.87 inches long

2.4mm female to 2.4mm female bulkhead adapter part number FMAD1159 from Fairview Microwave is in-stock and ships same day. This Fairview 2.4mm to 2.4mm adapter has a female to female gender configuration. FMAD1159 2.4mm female to 2.4mm female adapter operates to 50 GHz. The Fairview Microwave RF adapter provides good VSWR of 1.3:1 maximum. The 2.4mm connector mates mechanically with commercially available 1.85mm (V) connectors. Our RF 2.4mm to 2.4mm bulkhead adapter allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

•					
Description	Min	Тур	Мах	Units	
Frequency Range	DC		50	GHz	
VSWR			1.3:1		
Insertion Loss			0.3	dB	

Electrical Specification Notes: Values at 25°C, sea level.

Mechanical Specifications

Size Length	0.866 in [22 mm]			
Description	Connector 1	Connector 2		
Туре	2.4mm Female	2.4mm Female		
Polarity	Standard	Standard		
Mating Cycles	500	500		

Material Specifications

Description	Connector 1	Connector 2 2.4mm Female		
Туре	2.4mm Female			
Contact Material	rial Beryllium Copper Beryllium C			
Insulation Material	PEI	PEI		
Outer Contact Material	Passivated Stainless Steel	Passivated Stainless Steel		

Environmental Specifications

Temperature Operating Range



Configuration:

- 2.4mm Female Connector 1
- 2.4mm Female Connector 2
- 50 Ohm
- Straight Body Geometry
- Bulkhead Mount Method

Features:

- VSWR of 1.3:1 max up to 50 GHz
- Plated Beryllium Copper Contact

Applications:

- General Purpose Test
- Rack Mounted Equipment

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Compliance Certifications (see product page for current document)

Plotted and Other Data


Notes:

2.4mm Female to 2.4mm Female Bulkhead Adapter 0.87 inches long from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 2.4mm Female to 2.4mm Female Bulkhead Adapter 0.87 inches long FMAD1159


URL: https://www.fairviewmicrowave.com/2.4mm-female-2.4mm-female-bulkhead-adapter-fmad1159-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.









0.87 inches long

3. DIMENSIONS ARE IN INCHES [mm].							
DWG NO CAGE CODE 3FKR5					FKR5		
CAD FILE	03/11/19	SHEET	1 OF 1	SCAL	E N/A	SIZE A	7361

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689