

FMAD1244 DATA SHEET

N Female to N Female 4 Hole Flange Adapter with Passivated Stainless Steel Body

Type N female to type N female 4 hole flange adapter part number FMAD1244 from Fairview Microwave is in-stock and ships same day. This Fairview type N to type N adapter has a female to female gender configuration and is built of durable stainless steel. FMAD1244 type N female to type N female adapter operates to 18 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.2:1 maximum. Our RF type N to type N 4 hole flange adapter allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		18	GHz
VSWR			1.2:1	

Mechanical Specifications

2	ΙZ	е

Length Width		1.752 in [44.5 mm] 1 in [25.4 mm]
-----------------	--	--------------------------------------

Description	Connector 1	Connector 2
Туре	N Female	N Female
Polarity	Standard	Standard
Mating Cycles	500	500

Material Specifications

Connector 1	Connector 2
N Female	N Female
Beryllium Copper	Beryllium Copper
Gold over Nickel	Gold over Nickel
4 µin over 80µin	4 μin over 80μin
PTFE	PTFE
Passivated Stainless Steel	Passivated Stainless Steel
Passivated Stainless Steel	Passivated Stainless Steel
	N Female Beryllium Copper Gold over Nickel 4 µin over 80µin PTFE Passivated Stainless Steel

Configuration:

- N Female Connector 1
- N Female Connector 2
- 50 Ohm
- Straight Body Geometry
- 4 Hole Flange Mount Method

Features:

- VSWR of 1.2:1 max up to 18 GHz
- 4 µin over 80µin contact plating
- Gold over Nickel Plated Beryllium Copper Contact

Applications:

- General Purpose Test
- Rack Mounted Equipment

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com





Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

N Female to N Female 4 Hole Flange Adapter with Passivated Stainless Steel Body from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: N Female to N Female 4 Hole Flange Adapter with Passivated Stainless Steel Body FMAD1244

URL: https://www.fairviewmicrowave.com/n-female-n-female-4-hole-flange-adapter-fmad1244-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





