

# Low PIM QN Male (Plug) to TNC Female (Jack) Adapter



## **FMAD1712**

## Configuration

- · QN Male Connector 1
- TNC Female Connector 2
- 50 Ohm

#### **Features**

- · Typical PIM levels of -160 dBc
- · Silver Plated Beryllium Copper Contact

## **Applications**

- Enables Between Series Connections
- · General Purpose Test

- · Low PIM Design
- · Straight Body Geometry
- Max of VSWR 1.15:1 at 3GHz. Max of VSWR 1.2:1 at 6GHz

#### Low PIM Applications

## **Description**

QN male to TNC female adapter part number FMAD1712 from Fairview Microwave is in-stock and ships same day. This Fairview QN to TNC adapter has a male to female gender configuration in a low PIM design. FMAD1712 QN male to TNC female adapter operates to 6 GHz. The Fairview Microwave RF adapter provides a passive intermodulation of -160 dBc typical.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

#### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
Impedance		50 Ohm		
Passive Intermodulation		-160		dBc
Dielectric Withstanding Voltage (AC)			1,000	Vrms

## **Mechanical Specifications**

Size

 Length
 1.38 in [35.00 mm]

 Width
 0.71 in [18.00 mm]

 Height
 0.71 in [18.00 mm]

 Weight
 0.04 lbs [16.57 g]

Description	escription Connector 1 C	
Туре	QN Male	TNC Female
Polarity	Standard	Standard



# Low PIM QN Male (Plug) to TNC Female (Jack) Adapter



## **FMAD1712**

### **Material Specifications**

	Connector 1		Connector 2	
Description	Material	Plating	Material	Plating
Туре	QN Male		TNC Female	
Contact	Beryllium Copper	Silver	Beryllium Copper	Silver
Insulation	PTFE		PTFE	
Outer Conductor			Beryllium Copper	Silver
Body	Brass	Tri-Metal	Brass	Tri-Metal
Coupling Nut	Brass	Tri-Metal		

### **Environmental Specifications**

**Temperature** 

Operating Range -40 to +155 °C

Compliance Certifications (see product page for current document)

## **Plotted and Other Data**

Low PIM QN Male (Plug) to TNC Female (Jack) Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF ondemand.

For additional information on this product, please click the following link: Low PIM QN Male (Plug) to TNC Female (Jack) Adapter FMAD1712

URL: https://www.fairviewmicrowave.com/low-pim-qn-male-to-tnc-female-adapter-fmad1712-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

