

High Temperature Adapter 2.92mm Male to 3.5mm Female, 34.5GHz VSWR1.25, MIL-STD 348B with Stainless Steel Body

2.92mm male to 3.5mm female adapter part number FMAD1679 from Fairview Microwave is in-stock and ships same day. This Fairview 2.92mm to 3.5mm adapter has a male to female gender configuration in a high temperature adapter design. FMAD1679 2.92mm male to 3.5mm female adapter operates to 34.5 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.25:1 maximum. The 2.92mm connector mates mechanically with commercially available SMA and 3.5mm connectors.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		34.5	GHz
VSWR			1.25:1	
Insertion Loss			0.24	dB
Operating Voltage (AC)			250	Vrms
DWV (AC)			750	Vrms
Insulation Resistance	5,000			MOhms
RF Leakage			100	dB

Mechanical Specifications

Size	
Length	0.84 in [21.34 mm]
Width	0.31 in [7.87 mm]
Height	0.31 in [7.87 mm]
Weight	0.01 lbs [4.54 g]

Description	Connector 1	Connector 2
Type	2.92mm Male	3.5mm Female
Polarity	Standard	Standard
Mating Cycles, Min	500	500
Hex Size	8 mm	
Mating Torque	11.47 in-lbs min [1.30 Nm] min	7.1 to 9.7 in-lbs [0.80 to 1.10 Nm]
Contact Captivation Axial Force, Min	4.9 lbs [2.22 kg]	6.1 lbs [2.77 kg]
Coupling Proof Torque	15 in-lbs [1.7 Nm]	15 in-lbs [1.7 Nm]



Configuration:

- 2.92mm Male Connector 1
- 3.5mm Female Connector 2
- 50 Ohm
- High Temperature Adapter Design
- Straight Body Geometry

Features:

- VSWR of 1.25:1 max up to 34.5 GHz
- Gold over Nickel Plated Beryllium Copper Contact

Applications:

- Enables Between Series Connections
- General Purpose Test

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Material Specifications

Description	Connector 1	Connector 2
Type	2.92mm Male	3.5mm Female
Contact Material	Beryllium Copper	Beryllium Copper
Contact Plating	Gold over Nickel	Gold over Nickel
Insulation Material	PEI	PEI
Body Material	Stainless Steel	Stainless Steel
Body Plating	Passivated	Passivated
Coupling Nut Material	Stainless Steel	
Coupling Nut Plating	Passivated	

Environmental Specifications
Temperature

Operating Range
 Humidity
 Thermal Shock
 Salt Spray

-50 to +170 deg C
 MIL-STD-202, Method 206
 MIL-STD-202, Method 107, Condition B
 MIL-STD-202, Method 101, Condition B

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

High Temperature Adapter 2.92mm Male to 3.5mm Female, 34.5GHz VSWR1.25, MIL-STD 348B with Stainless Steel Body from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [High Temperature Adapter 2.92mm Male to 3.5mm Female, 34.5GHz VSWR1.25, MIL-STD 348B with Stainless Steel Body FMAD1679](#)

URL: <https://www.fairviewmicrowave.com/high-temperature-adapter-2.92mm-male-to-3.5mm-female-adapter-mil-std-202-method-206-34.5ghz-vswr1.25-mil-std-348b-with-stainless-steel-body-fmad1679-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

