

Low PIM RA 4.3-10 Male (Plug) to 4.3-10 Female (Jack) Adapter



FMAD1698

Configuration

- 4.3-10 Male Connector 1
- 4.3-10 Female Connector 2
- 50 Ohm
- Low PIM Design
- Right Angle Body Geometry

Features

- Typical PIM levels of -160 dBc
- Silver Plated Beryllium Copper Contact
- Max of VSWR 1.15:1 at 3GHz

Applications

- General Purpose Test
- Low PIM Applications

Description

RA 4.3-10 male to 4.3-10 female adapter part number FMAD1698 from Fairview Microwave is in-stock and ships same day. This Fairview 4.3-10 to 4.3-10 adapter has a male to female gender configuration in a low PIM design. FMAD1698 4.3-10 male to 4.3-10 female adapter operates to 6 GHz. The Fairview Microwave RF adapter provides a passive intermodulation of -160 dBc typical. This right angle 4.3-10 adapter allows for easier connections in tight spaces.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
Impedance		50 Ohm		
Passive Intermodulation		-160		dBc
Dielectric Withstanding Voltage (AC)			2,000	Vrms

Mechanical Specifications

Size

Length	1.47 in [37.40 mm]
Width	1.35 in [34.20 mm]
Height	0.87 in [22.00 mm]
Weight	0.18 lbs [83.32 g]

Description	Connector 1	Connector 2
Type	4.3-10 Male	4.3-10 Female
Polarity	Standard	Standard

Low PIM RA 4.3-10 Male (Plug) to 4.3-10 Female (Jack) Adapter



FMAD1698

Material Specifications

Description	Connector 1		Connector 2	
	Material	Plating	Material	Plating
Type	4.3-10 Male		4.3-10 Female	
Contact	Beryllium Copper	Silver	Beryllium Copper	Silver
Insulation	PTFE		PTFE	
Outer Conductor			Bronze	Tri-Metal
Body	Brass	Tri-Metal	Brass	Tri-Metal
Coupling Nut	Brass	Tri-Metal		

Environmental Specifications

Temperature

Operating Range -40 to +155 °C

Environmental Specification Notes:
IEC 61169-43

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Low PIM RA 4.3-10 Male (Plug) to 4.3-10 Female (Jack) Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Low PIM RA 4.3-10 Male \(Plug\) to 4.3-10 Female \(Jack\) Adapter FMAD1698](#)

URL: <https://www.fairviewmicrowave.com/low-pim-ra-4.3-10-male-to-4.3-10-female-adapter-fmad1698-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMAD1698 CAD Drawing

Low PIM RA 4.3-10 Male (Plug) to 4.3-10 Female (Jack) Adapter

