



# Medium Power Amplifier at 27 dBm Psat Operating from 26.5 GHz to 40 GHz with 2.92mm

The FMAM4067 is a medium power amplifier, operating from 26.5 to 40 GHz and desgined for use in a wide range of general purpose applications. Typical performance includes 27 dBm of saturated output power min. and 35 dB small signal gain. This power amplifier requires a +12V DC supply, is unconditionally stable, and operates over the temperature range of 0°C to 50°C. The thin film assembly features rugged stripline construction with select GaAs FET devices. The package supports field replaceable 2.92mm connectors and is desgined for high reliablilty meeting MIL-STD-202F environmental test conditions for Humidity, Shock, Vibration, and altitude.

# **Electrical Specifications**

(TA = +25°C, DC Voltage = 12Volts, DC Current = 3A)

Description	Min	Тур	Max	Unit
Frequency Range	26.5		40	GHz
Small Signal Gain	35			dB
Gain Flatness		±4		dB
Psat	+27			dBm
Noise Figure			10	dB
Impedance (Input)		50		Ohms
Impedance (Output)		50		Ohms
Input VSWR			2.5:1	
Output VSWR			2.5:1	
Operating DC Voltage		12		Volts
Operating DC Current		3		А
Operating Temperature Ra	nge 0		+50	°C

# **Mechanical Specifications**

Size
Length 2.22 in [56.39 mm]
Width 1.7 in [43.18 mm]
Height 0.6 in [15.24 mm]
Input Connector 2.92mm Female
Output Connector 2.92mm Female
Bias Connector Solder Pin

### **Environmental Specifications**

#### **Temperature**

Operating Range 0 to +50 deg C Storage Range +40 to +100 deg C

Humidity MIL-STD-202F, Method 103B, Condi-

tion B

Shock MIL-STD-202F, Method 213B, Condi-

tion B

Vibration MIL-STD-202F, Method 204D, Condi-

tion B

Altitude MIL-STD-202F, Method 105C, Condi-

tion B



#### Features:

- 26.5 to 40 GHz Frequency Range
- PSAT +27 dBm min.
- · Small Signal Gain: 35 dB min.
- Gain Flatness: ±4 dB typ.
- 50 Ohm Input and Output Matched
- 0 to 50°C Operating Temperature
- Unconditionally Stable
- Single DC Positive Supply
- Built-in DC Voltage Regulator
- Field Replaceable 2.92mm Female connectors

# Applications:

- Electronic Warfare
- Electronic Countermeasures
- Radar Systems
- Telecom Infrastructure
- Test Instrumentation
- Communication Systems
- Satellite Communications
- Microwave Radio Systems
- Driver Amplifier
- High Power Output Amplifier

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com






## Compliance Certifications (see product page for current document)

#### **Plotted and Other Data**

Notes:

- Values at 25 °C, sea level
- Heatsink Required for Proper Operation








# **Amplifier Power-up Precautions**

- 1.) Confirm that proper ESD precautions and controls are always in place before handling any Amplifier module.
- 2.) Confirm adequate thermal management is in place to effectively dissipate heat away from the Amplifier package. The Amplifier operational baseplate temperature must be within the operational temperature range stated in the Amplifier datasheet. Depending on the design and thermal requirements, using a heatsink with cooling fan is always recommended for safe reliable operation. A heat sink without a cooling fan may also be used. Damage caused from overheating will void the warranty.
- 3.) Confirm adequate system grounding is established. The DC power supply and Amplifier must have a common ground in order to operate properly.
- 4.) Power Amplifiers may require additional DC Current when initially powered-up. Depending on the design, the input current draw could range from an additional 10% to 100% above the maximum rated DC current of the Amplifier. This varies based on product part number.
- 5.) Confirm the DC power supply, if limited, is set to allow for additional start-up current that's rated for the Power Amplifier.
- 6.) Confirm the system is designed and calibrated for 50 ohms. Any impedance mismatch may cause performance issues.
- 7.) Perform a CALIBRATION (if required) with the loads before connecting the Amplifier to the Network Analyzer to ensure proper performance.
- 8.) Use a fixed attenuator between the signal source and input port of the Amplifier to optimize the input VSWR match.
- 9.) Confirm the input power level at the input port of the amplifier does not exceed the maximum rated limit for input power (as stated in the Amplifier datasheet).
  - P<sub>in</sub> for Small Signal Gain = P1dB-SSG-10 dB
  - P<sub>in</sub> for P1dB = P1dB-SSG+1 dB
- 10.) Confirm the Network Analyzer is always connected to the Amplifier first before DC power is applied to the Amplifier.
- 11.) As long as the input and output ports of the amplifier are connected to a 500hm load and RF signal power is applied, the Amplifier can be powered up with DC voltage.
- 12.) Confirm the Amplifier output load is matched for a 50 Ohm impedance and will not exceed the maximum rated VSWR or Return Loss limit for the Amplifier. Exceeding the maximum rated VSWR or Return Loss limit will result in reflected signal power that could damage the Amplifier and void the warranty.
- 13.) Power Amplifier connected to an Antenna for signal transmission It's strongly recommended to use a high power fixed attenuator pad or an Isolator between the output port of the Amplifier and input port to the antenna. Any reflected signal power due to impedance mismatch will likely damage the Amplifier and void the warranty.
- 14.) The attenuator or isolator used at the output port of the Amplifier must be rated to handle the output power level and operational frequency band of the amplifier.

#### **Typical Performance Data**











Medium Power Amplifier at 27 dBm Psat Operating from 26.5 GHz to 40 GHz with 2.92mm from Fairview Microwave is instock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Medium Power Amplifier at 27 dBm Psat Operating from 26.5 GHz to 40 GHz with 2.92mm FMAM4067


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order

URL: https://www.fairviewmicrowave.com/medium-power-amplifier-27dbm-35db-fmam4067-p.aspx

to implem	ent improve	ements.	Fairview	Microwa	ive reser	ves the rig	ht to m	ake su	ch cha	nges a	as req	uired.	Unless	otherwise
	specification													
suitability	of the part	describ	ed herein	for any	particula	ar purpose	, and Fa	airview	Micro	wave	does	not as	sume ar	ny liability
arising out	of the use	of any p	part or do	cumenta	ation.									








#### Notes:

- 1. Warranty void if removed.
- 2. The FMAM4067 includes a temperature sensor label on the side of the package. A heatsink and optional cooling fan is required for reliable operation of this design. The baseplate temperature should be monitored and maintained not exceed +50°C. Operation above +50°C baseplate temperature will likely cause eventual damage to the device. Any elevated temperature level running >50°C will become registered on the temperature sensor label. If the label is removed the warranty will be voided.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



T-Rev.D