

# FMAM7001 DATA SHEET

# Variable Gain Control Amplifier, 0.5 GHz to 2 GHz, GaAs FET, 40 dB Gain, 20 dB Variable Gain, +15 dBm P1dB, SMA

The FMAM7001 is an RF amplifier with voltage variable gain control that covers a broadband frequency from 0.5 GHz to 2 GHz. The module provides a continuously variable gain control of 20 dB over the entire frequency band which gives the Designer increased dynamic range and the ability to set signal levels. The low control current (typically less than 10 mA) simplifies control driver requirements. The design incorporates the use of GaAs FET and MMIC fixed-gain modules to provide low noise figure and medium power output over the entire frequency band. Typical performance for the 50 ohm design with 0V gain control includes 45 dB small signal gain, 3.5 dB noise figure, and +18 dBm output P1dB. DC Bias Voltage ranges from +12V to +15V with 250 mA current, and variable gain control voltage ranges from 0V for maximum gain to +5V for minimum gain. The rugged Mil Grade aluminum package supports SMA female connectors, has an operational temperature range of 0°C to +50°C, and is designed to meet a series of environmental conditions including Altitude, Vibration, Humidity, and Shock.

# **Electrical Specifications** (TA = +25°C, DC Voltage = 15Volts, DC Current = 250mA)

Description	Minimum	Typical	Maximum	Units
Frequency Range	0.5		2	GHz
Small Signal Gain	40	45		dB
Gain Flatness			±1.75	dB
Gain Control Range		20		dB
Output at P1dB*	+15	+18		dBm
P1dB at +5V Gain Contr	ol	12		dBm
Noise Figure*		3.5	4.5	dB
Input VSWR		1.2:1	2:1	
Output VSWR		1.5:1	2:1	
Operating DC Voltage	12	15	16	Volts
Control Voltage DC	0		5	Volts
Control DC Current		10		mA
Operating DC Current		250	320	mA

#### **Mechanical Specifications**

Size

Length 1.39 in [35.31 mm]
Width 1.4 in [35.56 mm]
Height 0.4 in [10.16 mm]
Weight 0.21 lbs [95.25 g]
Input Connector SMA Female
Output Connector SMA Female

## **Environmental Specifications**

Temperature

Operating Range 0 to +50 deg CStorage Range -40 to +100 deg C



#### **Features:**

- Variable Gain Amplifier
- Frequency Range 0.5 GHz to 2 GHz
- GaAs FET Semiconductor Technology
- Small Signal Gain 45 dB Typ
- Variable Gain 20 dB
- Output P1dB +18 dBm typ
- Noise Figure 3.5 dB typ
- DC Voltage +12 to +15 Vdc
- DC Control Voltage 0V to +5V
- 50 Ohm Design
- 0°C to +50°C Operating Temperature
- SMA Female Connectors
- Rugged Mil Grade Aluminum Package Design

### **Applications:**

- Aerospace & Defense
- Test & Measurment
- Microwave Radio Systems
- Military & Commercial Communication Systems
- Research & Development
- RF Front Ends
- SATCOM
- Wireless Communications
- Unmanned Systems

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Humidity MIL-STD-202F, Method 103B, Condition B
Shock MIL-STD-202F, Method 213B, Condition B
Vibration MIL-STD-202F, Method 204D, Condition B
Altitude MIL-STD-204F, Method 105C, Condition B

#### **Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:


- Values at +25 °C, sea level
- \*At 0V Gain Control
- DC Bias to the RF input may damage the Amplifier


301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689






#### **Typical Performance Data**











Variable Gain Control Amplifier, 0.5 GHz to 2 GHz, GaAs FET, 40 dB Gain, 20 dB Variable Gain, +15 dBm P1dB, SMA from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Variable Gain Control Amplifier, 0.5 GHz to 2 GHz, GaAs FET, 40 dB Gain, 20 dB Variable Gain, +15 dBm P1dB, SMA FMAM7001

URL: https://www.fairviewmicrowave.com/40-db-gain-variable-gain-amplifier-sma-fmam7001-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





