



Variable Gain Control Amplifier, 4 GHz to 12 GHz, GaAs FET, 40 dB Gain, 20 dB Variable Gain, +15 dBm P1dB, SMA

The FMAM7005 is an RF amplifier with voltage variable gain control that covers a broadband frequency from 4 GHz to 12 GHz. The module provides a continuously variable gain control of 20 dB over the entire frequency band which gives the Designer increased dynamic range and the ability to set signal levels. The low control current (typically less than 10 mA) simplifies control driver requirements. The design incorporates the use of GaAs FET and MMIC fixed-gain modules to provide low noise figure and medium power output over the entire frequency band. Typical performance for the 50 ohm design with 0V gain control includes 47 dB small signal gain, 3.5 dB noise figure, and +16.5 dBm output P1dB. DC Bias Voltage ranges from +12V to +15V with 360 mA current, and variable gain control voltage ranges from 0V for maximum gain to +5V for minimum gain. The rugged Mil Grade aluminum package supports SMA female connectors, has an operational temperature range of 0°C to +50°C, and is designed to meet a series of environmental conditions including Altitude, Vibration, Humidity, and Shock.

Electrical Specifications (TA = +25°C, DC Voltage = 15Volts, DC Current = 360mA)

Description	Minimum	Typical	Maximum	Units
Frequency Range	4		12	GHz
Small Signal Gain	40	47		dB
Gain Flatness			±2.75	dB
Gain Control Range		20		dB
Output at P1dB*	+15	+16.5		dBm
P1dB at +5V Gain Contro	ol	15		dBm
Noise Figure*		3.5	4	dB
Input VSWR		1.3:1	2:1	
Output VSWR		1.5:1	2:1	
Operating DC Voltage	12	15	16	Volts
Control Voltage DC	0		5	Volts
Control DC Current		10		mA
Operating DC Current		360		mA

Mechanical Specifications

Size

Lenath 1.4 in [35.56 mm] Width 1.39 in [35.31 mm] 0.4 in [10.16 mm] Height Weight 0.21 lbs [95.25 q] Input Connector SMA Female Output Connector SMA Female

Environmental Specifications Temperature

Operating Range Storage Range

0 to +50 deg C -40 to +100 deg C



Features:

- Variable Gain Amplifier
- Frequency Range 4 GHz to12 GHz
- GaAs FET Semiconductor Technology
- Small Signal Gain 47 dB Typ
- Variable Gain 20 dB
- Output P1dB +16.5 dBm Typ
- Noise Figure 3.5 dB Typ
- DC Voltage +12 to +15 Vdc
- DC Current 360 mA
- DC Control Voltage 0V to +5V
- DC Control Current < 10 mA
- 50 Ohm Design
- 0°C to +50°C Operating Temperature
- SMA Female Connectors
- Rugged Mil Grade Aluminum Package Design

Applications:

- Aerospace & Defense
- Test & Measurment
- Microwave Radio Systems
- Military & Commercial Communication Systems
- Research & Development
- RF Front Ends
- SATCOM
- Wireless Communications
- Unmanned Systems

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com






Shock Vibration MIL-STD-202F, Method 213B, Condition B MIL-STD-202F, Method 204D, Condition B

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

- Values at +25 °C, sea level
- *At 0V Gain Control
- DC Bias to the RF input may damage the Amplifier



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689


Copyright © 2020


REV 1.0 Page 2 of 5






Typical Performance Data











Variable Gain Control Amplifier, 4 GHz to 12 GHz, GaAs FET, 40 dB Gain, 20 dB Variable Gain, +15 dBm P1dB, SMA from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Variable Gain Control Amplifier, 4 GHz to 12 GHz, GaAs FET, 40 dB Gain, 20 dB Variable Gain, +15 dBm P1dB, SMA FMAM7005

URL: https://www.fairviewmicrowave.com/40-db-gain-variable-gain-amplifier-sma-fmam7005-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





