

# 27 MHz, Gooseneck Antenna, SMA Female Connector

# FMANOM1152

#### **Features**

- · 27 MHz Operating Frequency
- Flexible Gooseneck
- SMA Female Connector

#### **Applications**

- · Unmanned Vehicles
- · Manpack Radio Systems
- Secure Communications

- 1.5:1 VSWR
- · 10 Watt Max Input Power
- · Typical 3 dBi Gain
- · Surveillance Systems
- · Mobile Systems

#### **Description**

The FMANOM1152 from Fairview Microwave is an omnidirectional gooseneck antenna that features a flexible gooseneck mounting base. This flexible antenna can be bent and repositioned at any angle, allowing users to optimize signal reception and transmission in any environment. Our single-band gooseneck antenna with vertical polarization can operate at a center frequency of 27 MHz.

Fairview Microwave's FMANOM1152 gooseneck antenna has an impedance of 50 Ohms and a maximum input power of 10 Watts. This omnidirectional antenna is designed to withstand temperatures ranging from -40 to 80 degrees C. Our vertical polarized antenna has an overall length of 12.4 inches, a width of 1.5 inches, and a weight of 0.33 lbs. This gooseneck antenna is lightweight and compact, making it easy to transport and deploy in the field.

This vertically polarized antenna has a maximum input VSWR of 1.5:1. Our single-band gooseneck antenna with an SMA female connector has a nominal gain of 3 dBi. This FMANOM1152 antenna comes with a black TPE radome that offers a protective covering without compromising the antenna system's performance.

### Configuration

Design
Band Type
Radiation Pattern
Polarization
Connector Type

Gooseneck Single

Omni Directional

Vertical SMA Female

#### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Input VSWR			1.5:1	
Impedance		50		Ohms
Gain		3		dBi
Input Power			10	Watts

**TPE** 

# Mechanical Specifications Radome Material

Size	
Length	13 in [330.2 mm]
Width	1.5 in [38.1 mm]
Height	1.5 in [38.1 mm]
Weight	0.5 lbs [226.8 g]



# 27 MHz, Gooseneck Antenna, SMA Female Connector



# FMANOM1152

#### **Environmental Specifications**

Temperature

Operating Range

-40 to +80 deg C

Compliance Certifications (see product page for current document)

**Plotted and Other Data** 

Notes:

**Typical Radiation Pattern** 

#### **Appendix**

Electrical Downtilt: Angle in the antenna's elevation pattern in which the maximum gain occurs.

Gain: Antenna's average gain.

Front to Back Ratio @ 180°±30°: Average difference between the antenna's maximum gain and the maximum gain in the antenna's back lobe over ±30° angles.

Cross-polarization Ratio (dB): Typical difference between the co-polarization and cross-polarization gain across the sector's 3 dB Beam Width.

Dedicated to serving the needs of the Wireless Internet Service Provider (WISP) market, KP Performance Antennas offers purpose built products that reliably perform in the field. KP Performance Antennas product line consists of Yagi, Grid, Omni, Dish and other style antennas that operate in the 900 MHz, 2.4 GHz, 3 GHz, and 5 GHz frequencies.

27 MHz, Gooseneck Antenna, SMA Female Connector from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF ondemand.

For additional information on this product, please click the following link: 27 MHz, Gooseneck Antenna, SMA Female Connector FMANOM1152

URL: https://www.fairviewmicrowave.com/3-dbi-gooseneck-antenna-sma-connector-fmanom1152-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

