

**400-868 MHz Rubber Duck Antenna, 2.5 dBi gain,
TNC Male Connector, Vertical Polarization**

Fairview Microwave's FMANRBD1016 is a vertical polarized antenna that ships same day from our ISO 9001:2015 certified facility. This directional antenna has TNC male connector. The FMANRBD1016 is a single band antenna operating from 400 to 868 MHz with 2.5 dBi gain.

Fairview Microwave's antenna with 400 to 868 MHz frequency range has a maximum input VSWR of 1.5:1. The FMANRBD1016 antenna has a black radome made of TPE, an overall length of 6.48 in, width of 0.500 in, and weighs 0.022 lbs.

Use our on-line ordering system to purchase your FMANRBD1016 antenna 24 hours a day with same-day shipping and no MOQs (minimum order quantities).

Configuration

Design	Rubber Duck
Gain	2.5
Polarization	Vertical
Connector Type	TNC Male

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	400		868	MHz
Input VSWR			1.5:1	
Impedance		50		Ohms
Gain		2.5		dBi
Input Power			50	Watts

Mechanical Specifications

Radome Material	TPE
Size	
Length	6.48 in [164.59 mm]
Width	0.5 in [12.7 mm]
Height	0.5 in [12.7 mm]
Weight	0.022 lbs [9.98 g]

Environmental Specifications

Temperature	
Operating Range	-40 to +80 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:



Features:

- 400 MHz to 868 MHz, 2.5 dBi Gain
- TNC-Male connector
- Heliflex whip antenna
- Plug and play
- 50W power handling
- VSWR < 1.5:1
- Vertical polarization
- Black

Applications:

- PtP or PtMP applications
- Trunking for two-way radio comms
- UHF applications
- Public Safety / Emergency services
- Tetra and P-25 applications exclusively supported
- Land and Private mobile radio (LMR) (PMR)
- Fixed and mobile services

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com


400-868 MHz Rubber Duck Antenna, 2.5 dBi gain, TNC Male Connector, Vertical Polarization from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [400-868 MHz Rubber Duck Antenna, 2.5 dBi gain, TNC Male Connector, Vertical Polarization FMANRBD1016](#)

URL: <https://www.fairviewmicrowave.com/2.5-dbi-rubber-duck-antenna-400-868-mhz-tnc-connector-fmanrbd1016-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





REVISION		DATE	CHANGED BY	APPROVED BY
ZONE	REV.	DESCRIPTION	INITIAL RELEASE	
	A		03/02/2023	KHIETPAS

<p>Fairview Microwave® an INFINITE® brand</p> <p>Website: www.FairviewMicrowave.com Phone: 1.800.715.4396 1.972.649.6678</p>		<p>INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5</p> <p>SCALE: NONE</p> <p>SHEET: 1 OF 1</p>		
<p>DESCRIPTION: 400 - 868 MHz, Rubber duck Antenna, 2.5 dBi, with TNC Male</p>				
SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	3FKR5	DFRISIELLO	FMANRBD1016	A

UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

.X = ±.2	[.5]	FRACTIONS
.XX = ±.02	[.5]	± 1/32
.XXX = ±.005	[.13]	ANGLES ± 1°

CABLE LENGTH TOLERANCES:

<12 [305]	±.125 [-0]
>12 [305] ≤ 60 [1524]	±.25 [-0]
>60 [1524] ≤ 120 [3048]	±.5 [-0]
>120 [3048] ≤ 300 [7620]	±1.0 [-0]
>300 [7620]	±.5% [-0]

ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.