

0 to 70 dB Step Attenuator With a 10 dB Step BNC Female Connectors Rated Up To 2.2 GHz and Up to 2 Watts in a Rotary Design

The FMAT1022 is a Step Attenuator that has 70 dB of total attenuation with 10 dB step size and rotary dial design across a frequency range from DC to 2.2 GHz. The design is tried and true technology that offers exceptional performance characteristics that include 0.5 dB maximum insertion loss, and a maximum VSWR of 1.4:1 at 2.2 GHz. The design also features excellent attenuation accuracy with \pm 0.4 dB typical at 2.2 GHz. The Chem film Aluminum alloy package has BNC Female connectors, and operates within the temperature range of -20°C to 80°C.

Electrical Specifications

•				
Description	Min	Тур	Max	Units
Frequency Range	DC		2.2	GHz
Impedance		50		Ohms
Insertion Loss			0.5	dB
Attenuation Value		dB		
Step Size	10			dB
Step Type				
Accuracy Statement	±0.5 dB or 3% (Whichever is greater)			
Input Power			2	Watts
Input Power, Peak			1	KWatts

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Range	DC to 1	1 to 2.2				GHz
Insertion Loss	0.3	0.5				dB
VSWR	1.2:1	1.4:1				

Mechanical Specifications

Length Width	2.67 in [67.82 mm] 1.5 in [38.1 mm]
Weight	0.57 lbs [258.55 g]
Body Material and Plating	Aluminum, Chem Film

Connectors

C:---

Description	Connector 1	Connector 2
Туре	BNC Female	BNC Female

Environmental Specifications

Temperature

Operating Range

-20 to 85 deg C

FMAT1022 DATA SHEET



Features:

- 10 dB steps from 0 to 70 dB Attenuation
- Rotary Dial Control
- ±0.5 dB or 3% Attenuation Accuracy
- BNC Female Connectors
- -20°C to +80°C Operating Temperature

Applications:

- Instrumentation
- Precision Measurements
- Prototyping and Characterization
- Production Systems

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data


VSWR 3.0 2.8 2.6 2.4 2.2 2.0 1.8 1.6 1.4 1.2 1.0 0.6 0.0 GHz 0.3 0.8 1.1 1.4 1.7 1.9 2.2



1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







0 to 70 dB Step Attenuator With a 10 dB Step BNC Female Connectors Rated Up To 2.2 GHz and Up to 2 Watts in a Rotary Design from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 0 to 70 dB Step Attenuator With a 10 dB Step BNC Female Connectors Rated Up To 2.2 GHz and Up to 2 Watts in a Rotary Design FMAT1022


URL: https://www.fairviewmicrowave.com/70db-step-attenuator-10db-bnc-female-dc-2.2-ghz-2-watts-fmat1022-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689