

40 dB RF Fixed Attenuator SMA Male (Plug) to SMA Female (Jack), DC to 12 GHz Rated to 2 Watt, Stainless Steel Body, 1.35:1 VSWR



FMAT7466-40

Features

- DC to 12 GHz Range
- Attenuation 40 ±3 dB
- 2 Watts (CW) Power
- VSWR <1.35:1

Applications

- Precision Measurements
- Production Systems
- Instrumentation
- Prototyping and Characterization

Description

Fairview Microwave carries a wide range of fixed attenuators with a broad selection of attenuation levels, frequency ranges, and power dissipation ranges. RF microwave attenuators (also known as RF pads) lower the amplitude of a signal (attenuate) a known amount and can be used in a wide variety of applications. These attenuators pads are used when a signal needs to be reduced to protect measurement equipment or other circuitry, to extend the range of power meters and amplifiers, and to impedance match circuits by reducing the VSWR seen by adjacent components. RF attenuators can prevent signal overload in amplifiers, receivers and detectors, adjusting the signal level to a range that is optimal.

Few RF components are as commonly used as fixed coaxial attenuators, and Fairview Microwave carries one of the largest in-stock varieties and ships them same day. The 40 dB Fixed Attenuators FMAT7466-40 is rated to 2 Watts and operates from DC to 12 GHz. The versatile coaxial package uses SMA male to SMA female connectors.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		12	GHz
Impedance		50		Ohms
Nominal Attenuation		40		dB
Input Power, CW			2	Watts

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 2	2 to 5	5 to 10	10 to 12		GHz
VSWR, Max	1.15:1	1.25:1	1.35:1	1.35:1		
Attenuation Accuracy, Typ	0.6	1	1.5	3		dB

Mechanical Specifications

Size

Length	1.201 in [30.51 mm]
Width/Diameter	0.315 in [8 mm]
Height	0.315 in [8 mm]
Weight	0.0129 lbs [5.85 g]
Body Material and Plating	Passivated Stainless Steel

Configuration

Design	Fixed, Bidirectional
--------	----------------------

40 dB RF Fixed Attenuator SMA Male (Plug) to SMA Female (Jack), DC to 12 GHz Rated to 2 Watt, Stainless Steel Body, 1.35:1 VSWR



FMAT7466-40

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	SMA Female
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Body Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel

Environmental Specifications

Temperature

Operating Range -50 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data

40 dB RF Fixed Attenuator SMA Male (Plug) to SMA Female (Jack), DC to 12 GHz Rated to 2 Watt, Stainless Steel Body, 1.35:1 VSWR from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [40 dB RF Fixed Attenuator SMA Male \(Plug\) to SMA Female \(Jack\), DC to 12 GHz Rated to 2 Watt, Stainless Steel Body, 1.35:1 VSWR FMAT7466-40](#)

URL: <https://www.fairviewmicrowave.com/40db-fixed-attenuator-sma-male-sma-female-2-watts-fmat7466-40-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMAT7466-40 CAD Drawing

40 dB RF Fixed Attenuator SMA Male (Plug) to SMA Female (Jack), DC to 12 GHz Rated to 2 Watt, Stainless Steel Body, 1.35:1 VSWR

