

0 to 20 dB Variable Attenuator SMA Female to SMA
Female from 10.7 GHz to 14.5 GHz Rated to 5 Watts



FMAT7501-20

Features

- 20 dB Attenuation Level
- Rotary Dial Design for Continuous Adjustment Flat Across Frequency Range
- Frequency Range 10.7 GHz to 14.5 GHz
- SMA Female Connectorized Design
- Max VSWR 1.5:1
- Max Power Rating: 5W (CW)

Applications

- Instrumentation
- Precision Measurements
- Prototyping and Characterization
- Production Systems

Description

FMAT7501-20 from Fairview Microwave is a continuously variable attenuator that has 20 dB of total attenuation with rotary dial design for continuous attenuation level adjustment with +/- 1.5 dB flatness across a frequency Range from 10.7 GHz to 14.5 GHz. With SMA female connectors, this RF variable attenuator design is tried and true technology that offers exceptional RF performance characteristics that include 0.5 dB maximum insertion loss and a maximum VSWR of 1.5:1 and rated at 5 Watts (CW). Continuously variable attenuators are part of the comprehensive RF attenuator product offerings from Fairview Microwave which are available in stock and ready for same day shipment.

Configuration

Design: Continuously Variable Attenuator
Body Material and Plating: Aluminum

Electrical Specifications Values at 25°C, sea level

Description	Minimum	Typical	Maximum	Units
Frequency Range	10.7		14.5	GHz
Impedance		50		Ohms
Attenuation Value		0 to 20		dB
Step Type		Dial		
Input Power (CW)			5	Watts
Peak Power			3	kWatts
Insertion Loss			0.5	dB
VSWR			1.5:1	

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Range	10.7 to 14.5					GHz
Attenuation Accuracy	1.5					dB

Mechanical Specifications

Temperature

Size

Length: 2 in [50.8 mm]

0 to 20 dB Variable Attenuator SMA Female to SMA
Female from 10.7 GHz to 14.5 GHz Rated to 5 Watts



FMAT7501-20

Width	1.25 in [31.75 mm]
Height	0.5 in [12.7 mm]
Weight	0.02 lbs [9.07 g]

Connectors

Description	Connector 1	Connector 2
Type	SMA Female	SMA Female

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

- Notes:
- Values at 25 °C, sea level

0 to 20 dB Variable Attenuator SMA Female to SMA Female from 10.7 GHz to 14.5 GHz Rated to 5 Watts from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [0 to 20 dB Variable Attenuator SMA Female to SMA Female from 10.7 GHz to 14.5 GHz Rated to 5 Watts FMAT7501-20](#)

URL: <https://www.fairviewmicrowave.com/20db-continuously-variable-attenuator-sma-female-sma-female-5-watts-fmat7501-20-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMAT7501-20 CAD Drawing

0 to 20 dB Variable Attenuator SMA Female to SMA Female from 10.7 GHz to 14.5 GHz Rated to 5 Watts

