

## Low Loss TNC Female Bulkhead to RA MMCX Plug Cable LMR-100 Coax



### FMC00154

#### Configuration

- Connector 1: TNC Female Bulkhead
- Connector 2: MMCX Plug Right Angle
- Cable Type: LMR-100A
- Coax Flex Type: Flexible

#### Features

- Max Frequency 3 GHz
- Shielding Effectivity > 90 dB
- 66% Phase Velocity
- Double Shielded
- PVC Jacket

#### Applications

- General Purpose
- Laboratory Use

#### Description

The TNC female bulkhead to RA MMCX plug cable using LMR-100 coax, part number FMC00154, from Fairview Microwave is in-stock and ships same day. This Fairview TNC to MMCX cable assembly has a female to plug gender configuration with 50 ohm flexible LMR-100A coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC00154 TNC female to MMCX plug cable assembly operates to 3 GHz. The right angle MMCX interface on the LMR-100A cable allows for easier connections in tight spaces. Our RF cable assembly with TNC bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		66		%
RF Shielding	90			dB
Group Delay		1.54 [5.05]		ns/ft [ns/m]
Capacitance		30.8 [101.05]		pF/ft [pF/m]
Inductance		0.077 [0.25]		uH/ft [uH/m]
DC Resistance Inner Conductor		81 [265.75]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		9.5 [31.17]		Ohms/1000ft [Ohms/Km]

Low Loss TNC Female Bulkhead to RA  
MMCX Plug Cable LMR-100 Coax



**FMC00154**

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Jacket Spark			2,000	Vrms

**Specifications by Frequency**

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
			Frequency					MHz	
FMC00154	Custom Lengths Available	Insertion Loss (Typ.)	0.07	0.12	0.165	0.24	0.434	dB/ft	
			0.23	0.38	0.55	0.79	1.43	dB/m	
FMC00154-24	24 inch	Insertion Loss (Typ.)	0.44	0.53	0.63	0.78	1.17	dB	0.071
FMC00154-36	36 inch	Insertion Loss (Typ.)	0.51	0.65	0.8	1.02	1.61	dB	0.08
FMC00154-48	48 inch	Insertion Loss (Typ.)	0.58	0.76	0.96	1.26	2.04	dB	0.089
FMC00154-100CM	100 CM	Insertion Loss (Typ.)	0.53	0.68	0.85	1.09	1.73	dB	0.083
FMC00154-200CM	200 CM	Insertion Loss (Typ.)	0.76	1.06	1.39	1.88	3.15	dB	0.113

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.1 dB
Loss due to Connector 2:	0.2 dB
Base Weight:	0.062 pounds
Additional Weight per Inch:	0.00075 pounds

**Mechanical Specifications**

**Cable Assembly**

Weight 0.062 lbs [28.12 g]

**Cable**

Cable Type	LMR-100A
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel
Dielectric Type	PE
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	PVC, Black
Jacket Diameter	0.11 in [2.79 mm]
One Time Minimum Bend Radius	0.25 in [6.35 mm]
Repeated Minimum Bend Radius	1 in [25.4 mm]
Bending Moment	0.1 lbs-ft [0.14 N-m]
Flat Plate Crush	10 lbs/in [0.18 Kg/mm]
Tensile Strength	15 lbs [6.8 Kg]

Low Loss TNC Female Bulkhead to RA  
MMCX Plug Cable LMR-100 Coax



**FMC00154**

**Connectors**

Description	Connector 1	Connector 2
Type	TNC Female Bulkhead	MMCX Plug Right Angle
Specification	MIL-STD-348	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Contact Material and Plating	Phosphor Bronze, Gold	Brass, Gold
Contact Plating Specification		30 μin minimum
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Brass, Nickel	
Body Material and Plating	Brass, Nickel	Brass, Gold
Body Plating Specification		3 μin minimum
Hex Size	5/8 in	

**Environmental Specifications**

Operating Range Temperature -40 to +85 deg C

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

## Low Loss TNC Female Bulkhead to RA MMCX Plug Cable LMR-100 Coax




### FMC00154

#### Typical Performance Data

#### How to Order

Part Number Configuration:



Example: FMC00154-12 = 12 inches long cable  
FMC00154-100cm = 100 cm long cable

Low Loss TNC Female Bulkhead to RA MMCX Plug Cable LMR-100 Coax from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Low Loss TNC Female Bulkhead to RA MMCX Plug Cable LMR-100 Coax FMC00154](#)

URL: <https://www.fairviewmicrowave.com/low-loss-tnc-female-bulkhead-to-ra-mmcx-plug-cable-lmr-100-coax-fmc00154-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

# FMC00154 CAD Drawing

Low Loss TNC Female Bulkhead to RA MMCX Plug Cable LMR-100 Coax

