



10-32 Male to BNC Female Cable RG316 Tan Coax with Heat Shrink

The 10-32 male to BNC female cable using RG-316 coax, part number FMC00487, from Fairview Microwave is in-stock and ships same day. This Fairview 10-32 to BNC cable assembly has a male to female gender configuration with 50 ohm flexible RG316 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC00487 10-32 male to BNC female cable assembly operates to 1 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Т	ур	Max	Un	its
Frequency Range	DC			1,000	MI	Hz
VSWR				1.4:1		
Velocity of Propagation		(59		%	6
Capacitance		29.4	96.46]	pF/ft [pF/m]
Operating Voltage (AC)				500	Vrr	ns
Jacket Spark				2,000	Vrr	ns

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	50	100	250	500	1,000	MHz
Insertion Loss (Typ.)	0.07	0.11	0.16	0.23	0.38	dB/ft
	0.23	0.36	0.52	0.75	1.25	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. The Insertion Loss includes an estimated insertion loss of 0.1dB per connector loss.

Mechanical Specifications

Cable Assembly

Cable

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
Number of Shields
Shield Layer 1
Jacket Material
Jacket Diameter

RG316
50 Ohms
Stranded
Copper Clad Steel, Silver
PTFE
1
Silver Plated Copper Braid
FEP, Tan
0.102 in [2.59 mm]



Configuration:

- 10-32 Male
- BNC Female
- RG316

Features:

- Max Frequency 1 GHz
- 69% Phase Velocity
- FEP Jacket

Applications:

- General Purpose
- · Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com





Connectors

Description	Connector 1	Connector 2		
Туре	10-32 Male	BNC Female		
Specification	MIL-C-39012	MIL-STD-348A		
Impedance	50 Ohms	50 Ohms		
Contact Material & Plating	Brass, Gold	Brass, Gold		
Contact Plating Spec.	MIL-G-45204	30 µin minimum		
Dielectric Type	PTFE	PTFE		
Body Material & Plating	Brass, Nickel	Brass, Nickel		
Body Plating Spec.	QQ-N-290	100 µin minimum		

Environmental Specifications

Temperature

Operating Range -55 to +200 deg C


Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:



Example: FMC00487-12 = 12 inches long cable

FMC00487-100cm = 100 cm long cable

10-32 Male to BNC Female Cable RG316 Tan Coax with Heat Shrink from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: 10-32 Male to BNC Female Cable RG316 Tan Coax with Heat Shrink FMC00487

URL: https://www.fairviewmicrowave.com/10-32-male-bnc-female-cable-rg316-coax-fmc00487-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





