

FMC0101240 DATA SHEET

N Male to N Male Cable LMR-240 Coax with Times Microwave Connectors

General purpose flexible LMR-240 cable assemblies are built using high quality connectors and Times Microwaves cable. These cable assemblies are built using double shielded flexible cable providing excellent shielding greater than 90 dB. These general purpose cables are intended for, lab use, equipment interconnect and anywhere that lower insertion loss and greater shielding effectiveness than standard RG type cable is required.

Electrical Specifications

| Description | Min | Т | ур | Max | Units | |
|-------------------------------|-----|--------------|--------|----------------------------------|-------|----------|
| Frequency Range | DC | | | 2.5 | | GHz |
| VSWR | | | | 1.35:1 | | |
| Velocity of Propagation | | 3 | 34 | | | % |
| RF Shielding | 90 | | | | | dB |
| Capacitance | | 24.2 | [79.4] | | pF/f | t [pF/m] |
| Inductance | | 0.06 [0.2] | | uH/ft [uH/m] | | |
| DC Resistance Inner Conductor | | 3.2 [10.5] | | Ω/1000ft [Ω/Km] | | |
| DC Resistance Outer Conductor | | 3.89 [12.76] | | $\Omega/1000$ ft [$\Omega/$ Km] | | |
| | | | | | | |

Mechanical Specifications

Cable Assembly

Diameter 0.875 in [22.23 mm]
Weight 0.166 lbs [75.3 g]

Cable

Cable Type
Impedance
Inner Conductor Type
Dielectric Type
Number of Shields
Shield Layer 1
Shield Layer 2
Jacket Material
Jacket Diameter

LMR-240 50 Ohms Solid PE (F) 2 Tinned Copper Aluminum Tape PE, Black

0.24 in [6.1 mm]

Connectors

| Description | Connector 1 | Connector 2 | | |
|---------------------------------|------------------------|------------------------|--|--|
| Туре | N Male | N Male | | |
| Configuration | Straight | Straight | | |
| Polarity | Standard | Standard | | |
| Impedance | 50 Ohms | 50 Ohms | | |
| Contact Material & Plating | Beryllium Copper, Gold | Beryllium Copper, Gold | | |
| Dielectric Type | PTFE | PTFE | | |
| Outer Cond Material & Plating | Brass, Tri-Metal | Brass, Tri-Metal | | |
| Coupling Nut Material & Plating | Brass, Tri-Metal | Brass, Tri-Metal | | |
| Hex Size | 13/16 inch | 13/16 inch | | |



Configuration:

- N Male
- N Male
- LMR-240

Features:

- N Male to N Male
- Times© LMR-240 Flexible Low Loss Coax
- Heat Shrink Booting
- VoP of 84%
- · Custom lengths available
- •

Applications:

- General Purpose
- Wireless Communications
- Lab Use
- Equipment Interconnect

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





Environmental Specifications

Temperature

Operating Range


-40 to +85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data



How to Order

Part Number Configuration:

FMC0101240 - xx uu

cm = Centimeters

chlank> = Inches

Length

Example: FMC0101240-12 = 12 inches long cable

FMC0101240-100cm = 100 cm long cable

N Male to N Male Cable LMR-240 Coax with Times Microwave Connectors from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: N Male to N Male Cable LMR-240 Coax with Times Microwave Connectors FMC0101240


URL: https://www.fairviewmicrowave.com/n-male-n-male-cable-lmr-240-coax-fmc0101240-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2016





| FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM | NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm]. | | | | | |
|---|---|-------|-------|-----------------|--------|------|
| N Male to N Male Cable LMR-240 Coax with Times Microwave Connectors | DWG NO FMC0101240 | | | CAGE CODE 3FKR5 | | |
| | CAD FILE 101014 | SHEET | SCALI | E N/A | SIZE A | 5568 |