

Low Loss N Male to TNC Male Cable LMR-195 Coax in 24 Inch with LF Solder

The type N male to TNC male 24 inch cable using LMR-195 coax, part number FMC0103195LF-24, from Fairview Microwave is in-stock and ships same day. This Fairview type N to TNC cable assembly has a male to male gender configuration with 50 ohm flexible LMR-195 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0103195LF-24 type N male to TNC male cable assembly operates to 2.5 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Min | Typ | Max | Units |
|-------------------------------|-----|--------------|--------|----------------------------------|
| Frequency Range | DC | | 2.5 | GHz |
| VSWR | | | 1.35:1 | |
| Velocity of Propagation | | 83 | | % |
| RF Shielding | 90 | | | dB |
| Capacitance | | 24.5 [80.38] | | pF/ft [pF/m] |
| Inductance | | 0.061 [0.2] | | uH/ft [uH/m] |
| DC Resistance Inner Conductor | | 5.36 [17.59] | | Ω /1000ft [Ω /Km] |
| DC Resistance Outer Conductor | | 5.9 [19.36] | | Ω /1000ft [Ω /Km] |

Mechanical Specifications

Cable Assembly

| | |
|---------|--------------------|
| Length* | 24 in [609.6 mm] |
| Weight | 0.17 lbs [77.11 g] |

Cable

| | |
|--------------------------------------|--------------------|
| Cable Type | LMR-195 |
| Impedance | 50 Ohms |
| Inner Conductor Type | Solid |
| Inner Conductor Material and Plating | Copper |
| Dielectric Type | PE (F) |
| Number of Shields | 2 |
| Shield Layer 1 | Tinned Copper |
| Shield Layer 2 | Aluminum Tape |
| Jacket Material | PE, Black |
| Jacket Diameter | 0.195 in [4.95 mm] |



Configuration:

- N Male
- TNC Male
- LMR-195

Features:

- Max Frequency 2.5 GHz
- Shielding Effectivity > 90 dB
- 83% Phase Velocity
- Double Shielded
- PE Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Connectors

| Description | Connector 1 | Connector 2 |
|----------------------------|------------------------|------------------------|
| Type | N Male | TNC Male |
| Impedance | 50 Ohms | 50 Ohms |
| Contact Material & Plating | Beryllium Copper, Gold | Beryllium Copper, Gold |
| Dielectric Type | PTFE | PTFE |
| Body Material & Plating | Brass, Tri-Metal | Brass, Silver |

Environmental Specifications

Temperature

Operating Range

-65 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FMC0103195LF - xx uu

cm = Centimeters
<blank> = Inches
Length

Example: FMC0103195LF-12 = 12 inches long cable
FMC0103195LF-100cm = 100 cm long cable

Low Loss N Male to TNC Male Cable LMR-195 Coax in 24 Inch with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [Low Loss N Male to TNC Male Cable LMR-195 Coax in 24 Inch with LF Solder FMC0103195LF-24](#)

URL: <https://www.fairviewmicrowave.com/standard-n-male-tnc-male-cable-lmr195-coax-fmc0103195lf-24-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.