

N Male to TNC Male Cable LMR-400 Coax with Times Microwave Connectors

The type N male to TNC male cable using LMR-400 coax, part number FMC0103400, from Fairview Microwave is in-stock and ships same day. This Fairview type N to TNC cable assembly has a male to male gender configuration with 50 ohm flexible LMR-400 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0103400 type N male to TNC male cable assembly operates to 6 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Min DC	Тур	Max 6	Units GHz
DC		6	CH ₇
		-	GIIZ
		1.35:1	
	85		%
90			dB
	23.9 [78.41]	pF/ft [pF/m]
	0.06 [0.2]		uH/ft [uH/m]
	1.39 [4.56]		<u>Ω/100</u> 0ft [Ω/Km]
	1.65 [5.41]		Ω/1000ft [Ω/Km]
	90	90 23.9 [78.41 0.06 [0.2] 1.39 [4.56]	85

Mechanical Specifications

Cable Assembly Length* Diameter Weight

Cable

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Shield Layer 1 Shield Layer 2 Jacket Material Jacket Diameter 0 in [0 mm] 0 in [0 mm] 0.16314 lbs [74 g]

LMR-400 50 Ohms Solid Copper Clad Aluminum PE (F) 1 Tinned Copper Aluminum Tape PE, Black 0.405 in [10.29 mm]



FMC0103400 DATA SHEET

Configuration:

- N Male
- TNC Male
- LMR-400

Features:

- Max Frequency 6 GHz
- Shielding Effectivity > 90 dB
- 85% Phase Velocity
- PE Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com Fairview Microwave

an INFINITG brand



Connectors

Description	Connector 1	Connector 2	
Туре	N Male	TNC Male	
Configuration	Straight	Straight	
Impedance	50 Ohms	50 Ohms	
Contact Material & Plating	Brass, Gold	Beryllium Copper, Silver	
Contact Plating Spec.	50µ″ Min		
Dielectric Type	PTFE	PTFE	
Outer Cond Material & Plating	Brass, Tri-Metal		
Body Material & Plating		Brass, Nickel	
Coupling Nut Material & Plating	Brass, Tri-Metal	Brass, Nickel	
Hex Size	13/16 inch		

Environmental Specifications

Temperature Operating Range


-55 to +85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data



How to Order

Part Number Configuration:



Example: FMC0103400-12 = 12 inches long cable FMC0103400-100cm = 100 cm long cable

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689






N Male to TNC Male Cable LMR-400 Coax with Times Microwave Connectors from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: N Male to TNC Male Cable LMR-400 Coax with Times Microwave Connectors FMC0103400


URL: https://www.fairviewmicrowave.com/n-male-tnc-male-cable-times-lmr-400-coax-fmc0103400-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

an INFINIT[©] brand

FMC0103400 DATA SHEET



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689