

FMC0203195LF DATA SHEET

Low Loss SMA Male to TNC Male Cable LMR-195 Coax with LF Solder

The SMA male to TNC male cable using LMR-195 coax, part number FMC0203195LF, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to TNC cable assembly has a male to male gender configuration with 50 ohm flexible LMR-195 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0203195LF SMA male to TNC male cable assembly operates to 3 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Т	ур	Max	ι	Inits
Frequency Range	DC			3		GHz
VSWR				1.35:1		
Velocity of Propagation		8	33			%
RF Shielding	90					dB
Capacitance		24.5	[80.38]	pF/f	t [pF/m]
Inductance		0.06	1 [0.2]		uH/f	t [uH/m]
DC Resistance Inner Conductor		5.36 [17.59]		Ω/1000ft [Ω/Km]		
DC Resistance Outer Conductor		5.9 [19.36]		Ω/1000ft [Ω/Km]		

Mechanical Specifications

Cable Assembly

Length* 0 in [0 mm] Weight 0.082 lbs [37.19 g]

Cable

LMR-195 Cable Type **Impedance** 50 Ohms Inner Conductor Type Solid Inner Conductor Material and Plating Copper Dielectric Type PE (F) Number of Shields 2 Shield Laver 1 Tinned Copper Shield Laver 2 Aluminum Tape Jacket Material PE, Black 0.195 in [4.95 mm] Jacket Diameter



Configuration:

- SMA Male
- TNC Male
- LMR-195

Features:

- Max Frequency 3 GHz
- Shielding Effectivity > 90 dB
- 83% Phase Velocity
- Double Shielded
- PE Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com






Connectors

Description	Connector 1	Connecto			
Туре	SMA Male	TNC Mal	e		
Impedance	50 Ohms	50 Ohm	S		
Contact Material & Plating	Brass, Gold	Beryllium Copp	er, Gold		
Contact Plating Spec.	50μ in. minimum				
Dielectric Type	PTFE	PTFE			
Body Material & Plating	Brass, Gold	Brass, Silv	/er		
Body Plating Spec.	3μ in. minimum				
Hex Size	5/16 inch				
Torque	4 in-lbs 0.45 Nm	1			
rironmental Specifi Temperature Operating Range		to +85 deg C			

Compliance Certifications (see product page for current document)

Plotted and Other Data Notes:

How to Order



Low Loss SMA Male to TNC Male Cable LMR-195 Coax with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Low Loss SMA Male to TNC Male Cable LMR-195 Coax with LF Solder FMC0203195LF


URL: https://www.fairviewmicrowave.com/standard-sma-male-tnc-male-cable-lmr195-coax-fmc0203195lf-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
Low Loss SMA Male to TNC Male Cable LMR-195 Coax	DWG NO FMC0203195LF			CAGE CODE 3FKR5		
with LF Solder	CAD FILE 101414	SHEET	SCALE	N/A	SIZE A	5568