

FMC0123240 **DATA SHEET**

N Male to RA QMA Male Cable LMR-240 Coax with **Times Microwave Connectors**

Electrical Specifications

Description		Min	Тур	Max	Units	
Frequency Range		DC		2.5	GHz	
VSWR				1.35:1		
Velocity of Propagation			84		%	
RF Shielding		90			dB	
Capacitance			24.2 [79.4]		pF/ft [pF/m]	
Inductance			0.06 [0.2]		uH/ft [uH/m]	
DC Resistance Inner Cor	ductor		3.2 [10.5]		Ω/1000ft [Ω/Km]	
DC Resistance Outer Cor	nductor		3.89 [12.76]		Ω/1000ft [Ω/Km]	



Configuration:

- N Male
- QMA Male Right Angle
- LMR-240

Mechanical Specifications

Cable Assembly

Weight 0.10725 lbs [48.65 g]

Cable Cable Type LMR-240 50 Ohms **Impedance** Inner Conductor Type Solid Inner Conductor Material and Plating Copper Dielectric Type PE (F) Number of Shields Shield Layer 1 **Tinned Copper**

Shield Layer 2 Aluminum Tape Jacket Material PE, Black

Jacket Diameter 0.24 in [6.1 mm]

Connectors

Description	Connector 1	Connector 2				
Туре	N Male	QMA Male				
Polarity	Standard	Standard				
Impedance	50 Ohms	50 Ohms				
Contact Material & Plating	Beryllium Copper, Gold	Phosphor Bronze, Gold				
Contact Plating Spec.	ASTM-B488					
Dielectric Type	PTFE	PTFE				
Outer Cond Material & Plating		Brass, Nickel				
Coupling Nut Material & Plating	Brass, Tri-Metal					
Coupling Nut Plating Spec.	QQ-N-290					
Hex Size	13/16 inch					
Body Material & Plating	Brass, Tri-Metal	Brass, Nickel				
Body Plating Spec.	QQ-N-290					
· · · · · · · · · · · · · · · · · · ·	· · · · · · · · · · · · · · · · · · ·	· · · · · · · · · · · · · · · · · · ·				

Environmental Specifications Temperature

Operating Range

-40 to +85 deg C

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com






Compliance Certifications (see product page for current document)

Plotted and Other Data


Notes:

Typical Performance Data



How to Order

Part Number Configuration:



Example: FMC0123240-12 = 12 inches long cable

FMC0123240-100cm = 100 cm long cable

N Male to RA QMA Male Cable LMR-240 Coax with Times Microwave Connectors from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: N Male to RA QMA Male Cable LMR-240 Coax with Times Microwave Connectors FMC0123240

URL: https://www.fairviewmicrowave.com/n-male-ra-qma-plug-cable-times-lmr-240-coax-fmc0123240-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
N Male to RA QMA Male Cable LMR-240 Coax with Times Microwave Connectors	DWG NO FMC0123240			CAGE CODE 3FKR5		
	CAD FILE 101614	SHEET	SCALI	E N/A	SIZE A	5568