

**SMA Male to SMA Male Cable LMR-240-UF Coax in 36 Inch**

**Electrical Specifications**

Description	Min	Typ	Max	Units
Frequency Range	DC		6	GHz
VSWR			1.35:1	
Velocity of Propagation		84		%
RF Shielding	90			dB
Capacitance		24.2 [79.4]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		4.28 [14.04]		$\Omega/1000ft$ [ $\Omega/Km$ ]
DC Resistance Outer Conductor		3.89 [12.76]		$\Omega/1000ft$ [ $\Omega/Km$ ]

**Mechanical Specifications**

**Cable Assembly**

Length	36 in [914.4 mm]
Diameter	0.375 in [9.53 mm]
Weight	0.13374 lbs [60.66 g]

**Cable**

Cable Type	LMR-240-UF
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	1
Shield Layer 1	Tinned Copper
Shield Layer 2	Aluminum Tape
Jacket Material	PE, Black
Jacket Diameter	0.24 in [6.1 mm]

**Connectors**

Description	Connector 1	Connector 2
Type	SMA Male	SMA Male
Configuration	Straight	Straight
Polarity	Standard	Standard
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Dielectric Type	PTFE	PTFE
Hex Size	5/16 In.	5/16 In.
Body Material & Plating	Stainless Steel	Stainless Steel

**Environmental Specifications**

**Temperature**

Operating Range	-40 to +85 deg C
-----------------	------------------



**Configuration:**

- SMA Male
- SMA Male
- LMR-240-UF


Fairview Microwave  
 1130 Junction Dr. #100  
 Allen, TX 75013  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

**Compliance Certifications** (visit [www.FairviewMicrowave.com](http://www.FairviewMicrowave.com) for current document)

**Plotted and Other Data**

Notes:

**Typical Performance Data**



**How to Order**

Part Number Configuration:

**FMC0202245 - xx uu**

cm = Centimeters  
 <blank> = Inches  
 Length


Example: FMC0202245-12 = 12 inches long cable  
 FMC0202245-100cm = 100 cm long cable

SMA Male to SMA Male Cable LMR-240-UF Coax in 36 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [SMA Male to SMA Male Cable LMR-240-UF Coax in 36 Inch FMC0202245-36](http://www.fairviewmicrowave.com/sma-male-sma-male-cable-lmr-240-uf-coax-fmc0202245-36)

URL: <http://www.fairviewmicrowave.com/sma-male-sma-male-cable-lmr-240-uf-coax-fmc0202245-36-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



<b>FAIRVIEW MICROWAVE INC.</b> ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE SMA Male to SMA Male Cable LMR-240-UF Coax in 36 Inch		DWG NO FMC0202245		CAGE CODE 3FKR5	
		CAD FILE 101414	SHEET	SCALE N/A	SIZE A 5568