



### SMA Male to MMCX Jack Cable RG-316 Coax

## **Electrical Specifications**

| Description             | Min | Тур         | Max | Units |  |  |  |
|-------------------------|-----|-------------|-----|-------|--|--|--|
| Frequency Range         | DC  |             | 3   | GHz   |  |  |  |
| VSWR                    |     | 1.35:1      |     |       |  |  |  |
| Velocity of Propagation |     | 70          |     | %     |  |  |  |
| Capacitance             | 3   | 32 [104.99] |     |       |  |  |  |

# **Mechanical Specifications**

**Cable Assembly** 

Weight 0.00926 lbs [4.2 g]

Cable

Cable Type RG-316 Impedance 50 Ohms Stranded Inner Conductor Type Inner Conductor Material and Plating Copper, Silver PTFE

Dielectric Type Number of Shields

Shield Layer 1 Silver Plated Copper Braid Jacket Material FEP, Tan

Jacket Diameter 0.098 in [2.49 mm]

## **Connectors**

| Description                | Connector 1        | Connector 2            |  |
|----------------------------|--------------------|------------------------|--|
| Туре                       | SMA Male           | MMCX Jack              |  |
| Polarity                   | Standard           | Standard               |  |
| Impedance                  | 50 Ohms            | 50 Ohms                |  |
| Contact Material & Plating | Brass, Gold        | Beryllium Copper, Gold |  |
| Contact Plating Spec.      | 50μ in. minimum    | 30μ in. minimum        |  |
| Dielectric Type            | PTFE               | PTFE                   |  |
| Hex Size                   | 5/16 inch          |                        |  |
| Torque                     | 4 in-lbs [0.45 Nm] |                        |  |
| Body Material & Plating    | Brass, Nickel      | Brass, Gold            |  |
| Body Plating Spec.         | 100μ in. minimum   | 3µ in. minimum         |  |
|                            |                    |                        |  |

## **Environmental Specifications**

**Temperature** 

Operating Range -65 to +165 deg C

**Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:

## **Configuration:**

- SMA Male
- MMCX Jack
- RG-316

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013


Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





## **Typical Performance Data**



SMA Male to MMCX Jack Cable RG-316 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: SMA Male to MMCX Jack Cable RG-316 Coax FMC0224315


URL: https://www.fairviewmicrowave.com/sma-male-mmcx-jack-cable-rg316-coax-fmc0224315-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

FMC0224315-100cm = 100 cm long cable





| FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM | NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  3. DIMENSIONS ARE IN INCHES [mm]. |       |       |                 |        |      |
|---|---|-------|-------|-----------------|--------|------|
| SMA Male to MMCX Jack Cable RG-316 Coax                           | DWG NO FMC0224315   |       |       | CAGE CODE 3FKR5 |        |      |
|   | CAD FILE 102814   | SHEET | SCALE | N/A             | SIZE A | 5568 |