

FMC0924174 **DATA SHEET**

MMCX Plug to MMCX Jack Cable RG-174 Coax

Electrical Specifications

Description	Min	Тур	Max	Units			
Frequency Range	DC		1,000	MHz			
VSWR		1.35:1					
Velocity of Propagation		66	%				
Capacitance	30	.94 [101.	51]	pF/ft [pF/m]			

Mechanical Specifications

Cable Assembly

Weight 0.00352 lbs [1.6 g]

Cable

Cable Type RG-174 Impedance Solid Inner Conductor Type

Inner Conductor Material and Plating

Dielectric Type Number of Shields Shield Layer 1 Jacket Material Jacket Diameter

50 Ohms

Copper Clad Steel

Tinned Copper Braid

PVC, Black

0.102 in [2.59 mm]

Connectors

Description	Connector 1	Connector 2			
Туре	MMCX Plug	MMCX Jack			
Polarity	Standard	Standard			
Impedance	50 Ohms	50 Ohms			
Contact Material & Plating	Brass, Gold	Beryllium Copper, Gold			
Contact Plating Spec.	30μ in. minimum	30µ in. minimum			
Dielectric Type	PTFE	PTFE			
Body Material & Plating	Brass, Gold	Brass, Gold			
Body Plating Spec.	3µ in. minimum	3µ in. minimum			

Environmental Specifications

Temperature

Operating Range -55 to +155 deg C

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

Plotted and Other Data

Notes:



Configuration:

- MMCX Plug
- MMCX Jack
- RG-174

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013


Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com



Length

Typical Performance Data



Example: FMC0924174-12 = 12 inches long cable

FMC0924174-100cm = 100 cm long cable

MMCX Plug to MMCX Jack Cable RG-174 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: MMCX Plug to MMCX Jack Cable RG-174 Coax FMC0924174

URL: http://www.fairviewmicrowave.com/mmcx-plug-mmcx-jack-cable-rg174-coax-fmc0924174-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
MMCX Plug to MMCX Jack Cable RG-174 Coax	DWG NO FMC0924174			CAGE CODE 3FKR5			
	CAD FILE	102814	SHEET	SCAL	E N/A	SIZE A	5568