

# FMC0451315LF **DATA SHEET**

# RA SMA Male to RA SSMA Male Cable RG-316 Coax with LF Solder

The RA SMA male to RA SSMA male cable using RG-316 coax, part number FMC0451315LF, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to SSMA cable assembly has a male to male gender configuration with 50 ohm flexible RG-316 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0451315LF SMA male to SSMA male cable assembly operates to 3 GHz. The right angle SMA and right angle SSMA interfaces on the RG-316 cable allow for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

## **Electrical Specifications**

Description	Min	Ty	ур Мах	Units
Frequency Range	DC		3	GHz
VSWR			1.35:1	

### **Mechanical Specifications**

**Cable Assembly** 

Length\* Weiaht

Cable

Cable Type **Impedance** 

Inner Conductor Type

Inner Conductor Material and Plating

Dielectric Type Number of Shields Shield Layer 1

Jacket Material

Jacket Diameter

0 in [0 mm]

0.02116 lbs [9.6 g]

RG-316 50 Ohms Stranded Copper, Silver PTFE

Silver Plated Copper Braid

FEP, Tan

0.098 in [2.49 mm]



# **Configuration:**

- SMA Male Right Angle
- SSMA Male Right Angle
- RG-316

### Features:

- Max Frequency 3 GHz
- FEP Jacket

# **Applications:**

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





#### **Connectors**

Description	Connector 1	Connector 2
Туре	SMA Male	SSMA Male
Configuration	Right Angle	Right Angle
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Brass, Gold	Brass, Gold
Contact Plating Spec.	50μ in. minimum	50μ in. minimum
Dielectric Type	PTFE	PTFE
Body Material & Plating	Brass, Nickel	Brass, Nickel
Body Plating Spec.	100μ in. minimum	100μ in. minimum
Hex Size	5/16 inch	1/4 inch

# **Environmental Specifications**

Temperature

Operating Range

-65 to +165 deg C

**Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:

#### **How to Order**

Part Number Configuration:

FMC0451315LF - xx uu | cm = Centimeters | chlank = Inches |

RA SMA Male to RA SSMA Male Cable RG-316 Coax with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: RA SMA Male to RA SSMA Male Cable RG-316 Coax with LF Solder FMC0451315LF


URL: https://www.fairviewmicrowave.com/standard-ra-sma-male-ra-ssma-male-cable-rg316-coax-fmc0451315lf-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
RA SMA Male to RA SSMA Male Cable RG-316 Coax with LF Solder	DWG NO FMC5151315LF			CAGE CODE 3FKR5			
	CAD FILE 032316	SHEET	SCALE	N/A	SIZE A	5568	