

FMC4141914 DATA SHEET

Test 3.5mm Male to 3.5mm Male Cable FM160FLEX Coax

The 3.5mm male to 3.5mm male cable using FM160FLEX coax, part number FMC4141914, from Fairview Microwave is in-stock and ships same day. This Fairview 3.5mm to 3.5mm cable assembly has a male to male gender configuration with 50 ohm flexible FM-160FLEX coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC4141914 3.5mm male to 3.5mm male cable assembly operates to 34 GHz. The triple shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Т	ур	Max	ι	Jnits
Frequency Range	DC			34		GHz
VSWR				1.4:1		
Velocity of Propagation		7	78			%
RF Shielding	90					dB
Capacitance		26 [85.3]		pF/ft [pF/m]		
Inductance		66 [216.54]		uH/f	uH/ft [uH/m]	

Performance by Frequency

-	-	-				
Description	F1	F2	F3	F4	F5	Units
Frequency	2.5	5	10	18	34	GHz
Insertion Loss (Max.)	0.23	0.33	0.49	0.66	0.98	dB/ft
	0.75	1.08	1.61	2.17	3.22	dB/m
Power Handling (Max.)	750	450	320	200	160	W

Mechanical Specifications

Cable Assembly

Length* 0 in [0 mm] Weight 0.13 lbs [58.97 g]

Cable

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
Number of Shields
Shield Layer 1
Shield Layer 2
Shield Layer 3

FM-160FLEX 50 Ohms Solid Copper, Silver

PTFE 3

Silver Plated Copper Aluminum Tape Silver Plated Copper



Configuration:

- 3.5mm Male
- 3.5mm Male
- FM-160FLEX

Features:

- Max Frequency 34 GHz
- Shielding Effectivity > 90 dB
- 78% Phase Velocity
- Triple Shielded
- ETFE Jacket

Applications:

- General Purpose
- Test & Measurement
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Jacket Material Jacket Diameter ETFE, Gray

0.16 in [4.06 mm]

One Time Minimum Bend Radius Typical Flex Cycles

0.8 in [20.32 mm]

10,000

Connectors

Description	Connector 1	Connector 2
Туре	3.5mm Male	3.5mm Male
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Beryllium Copper, G	Gold Beryllium Copper, Gold
Contact Plating Spec.	ASTM-B488 50μ In.	Min ASTM-B488 50µ In. Minimum
Dielectric Type	PCTFE	PCTFE
Body Material & Plating	Passivated Stainless	Steel Passivated Stainless Steel
Body Plating Spec.	SAE-AMS-2700	SAE-AMS-2700
Coupling Nut Material & Pla	ating Passivated Stainless	Steel Passivated Stainless Steel
Coupling Nut Plating Spec.	SAE-AMS-2700	SAE-AMS-2700
Hex Size	5/16 Inch	5/16 Inch
Torque	8 in-lbs 0.9 Nm	n 8 in-lbs 0.9 Nm

Environmental Specifications

Temperature

Operating Range

-45 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FMC4141914 - xx uu | cm = Centimeters | chlank> = Inches | Length

Example: FMC4141914-12 = 12 inches long cable

FMC4141914-100cm = 100 cm long cable





Test 3.5mm Male to 3.5mm Male Cable FM160FLEX Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Test 3.5mm Male to 3.5mm Male Cable FM160FLEX Coax FMC4141914


URL: https://www.fairviewmicrowave.com/3.5mm-male-3.5mm-male-cable-fm160flex-coax-fmc4141914-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
Test 3.5mm Male to 3.5mm Male Cable FM160FLEX	DWG NO FMC4141914			CAGE CODE 3FKR5		
Coax	CAD FILE 070915	SHEET	SCAL	E N/A	SIZE A	2233