

**Low Loss BNC Male to 7/16 DIN Male Cable**  
**LMR-240 Coax in 48 Inch with LF Solder**

The BNC male to 7/16 DIN male 48 inch cable using LMR-240 coax, part number FMC0815240LF-48, from Fairview Microwave is in-stock and ships same day. This Fairview BNC to 7/16 DIN cable assembly has a male to male gender configuration with 50 ohm flexible LMR-240 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0815240LF-48 BNC male to 7/16 DIN male cable assembly operates to 2.5 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

**Electrical Specifications**

| Description                   | Min | Typ          | Max    | Units                            |
|-------------------------------|-----|--------------|--------|----------------------------------|
| Frequency Range               | DC  |              | 2.5    | GHz                              |
| VSWR                          |     |              | 1.35:1 |                                  |
| Velocity of Propagation       |     | 84           |        | %                                |
| RF Shielding                  | 90  |              |        | dB                               |
| Capacitance                   |     | 24.2 [79.4]  |        | pF/ft [pF/m]                     |
| Inductance                    |     | 0.06 [0.2]   |        | uH/ft [uH/m]                     |
| DC Resistance Inner Conductor |     | 3.2 [10.5]   |        | $\Omega$ /1000ft [ $\Omega$ /Km] |
| DC Resistance Outer Conductor |     | 3.89 [12.76] |        | $\Omega$ /1000ft [ $\Omega$ /Km] |

**Mechanical Specifications**
**Cable Assembly**

Length\* 48 in [121.92 cm]

**Cable**

Cable Type LMR-240  
 Impedance 50 Ohms  
 Inner Conductor Type Solid  
 Inner Conductor Material and Plating Copper  
 Dielectric Type PE (F)  
 Number of Shields 2  
 Shield Layer 1 Tinned Copper  
 Shield Layer 2 Aluminum Tape  
 Jacket Material PE, Black  
 Jacket Diameter 0.24 in [6.1 mm]


**Configuration:**


- BNC Male
- 7/16 DIN Male
- LMR-240

**Features:**

- Max Frequency 2.5 GHz
- Shielding Effectivity > 90 dB
- 84% Phase Velocity
- Double Shielded
- PE Jacket

**Applications:**

- General Purpose
- Laboratory Use

**Cable Diagram:**


Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

**Connectors**

| Description                | Connector 1      | Connector 2      |
|----------------------------|------------------|------------------|
| Type                       | BNC Male         | 7/16 DIN Male    |
| Impedance                  | 50 Ohms          | 50 Ohms          |
| Contact Material & Plating | Brass, Gold      | Brass, Silver    |
| Dielectric Type            | PTFE             | PTFE             |
| Body Material & Plating    | Brass, Tri-Metal | Brass, Tri-Metal |

**Environmental Specifications**
**Temperature**

Operating Range

-65 to +85 deg C

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

**How to Order**

Part Number Configuration:

**FMC0815240LF - xx uu**

 \_\_\_\_\_ cm = Centimeters  
 <blank> = Inches  
 \_\_\_\_\_ Length


 Example: FMC0815240LF-12 = 12 inches long cable  
 FMC0815240LF-100cm = 100 cm long cable

Low Loss BNC Male to 7/16 DIN Male Cable LMR-240 Coax in 48 Inch with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [Low Loss BNC Male to 7/16 DIN Male Cable LMR-240 Coax in 48 Inch with LF Solder FMC0815240LF-48](#)

URL: <https://www.fairviewmicrowave.com/standard-bnc-male-7-16-din-male-cable-lmr240-coax-fmc0815240lf-48-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



|   |        |   |       |                    |             |
|---|--------|---|-------|--------------------|-------------|
| <b>FAIRVIEW MICROWAVE INC.</b><br>ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM                 |        | NOTES:<br>1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.<br>2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.<br>3. DIMENSIONS ARE IN INCHES [mm]. |       |                    |             |
| TITLE<br>Low Loss BNC Male to 7/16 DIN Male Cable LMR-240<br>Coax in 48 Inch with LF Solder |        | DWG NO<br>FMC0815240LF  |       | CAGE CODE<br>3FKR5 |             |
| CAD FILE  | 102814 | SHEET   | SCALE | N/A                | SIZE A 5568 |